

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252709

Luminaire Tested: P3AS20R359030D010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1252709
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R359030D010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R35 optic, 3000K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 870.0 lumens
Efficiency: N/A
Efficacy: 30.2 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1252709

CATALOG NUMBER: P3AS20R359030D010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1252709

CATALOG NUMBER: P3AS20R359030D010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	109	107	112	109	107	106	105	104	102		102	100	99		98
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94
3	105	99	95	91	103	98	94	90	95	92	89		93	90	88		91
4	100	94	89	85	99	93	88	85	91	87	84		89	85	83		87
5	96	89	84	80	95	88	83	80	86	82	79		85	81	78		83
6	92	85	80	76	91	84	79	76	83	78	75		81	77	75		80
7	89	81	76	72	88	80	75	72	79	75	71		78	74	71		77
8	85	77	72	69	84	77	72	68	76	71	68		75	71	68		74
9	82	74	69	66	81	74	69	65	73	68	65		72	68	65		71
10	79	71	66	63	78	71	66	63	70	66	63		69	65	62		69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	438781
5°	421703
10°	367439
15°	281432
20°	188293
25°	113934
30°	65377
35°	36540
40°	19436
45°	10017
50°	4810
55°	3785
60°	3640
65°	3009
70°	3206
75°	2796
80°	3157
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10017 cd/sqm

TEST NUMBER: P1252709

CATALOG NUMBER: P3AS20R359030D010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	174.3	20.0
10°-20°	337.8	38.8
20°-30°	221.2	25.4
30°-40°	89.7	10.3
40°-50°	26.9	3.1
50°-60°	9.2	1.1
60°-70°	6.1	0.7
70°-80°	3.6	0.4
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	733.3	84.3
0°-40°	823.0	94.6
0°-60°	859.0	98.7
0°-90°	870.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	870.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2001	
5°	1916	174
15°	1240	338
25°	471	221
35°	136	90
45°	32	27
55°	10	9
65°	6	6
75°	3	4
85°	1	1
90°	0	

TEST NUMBER: P1252709

CATALOG NUMBER: P3AS20R359030D010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2001.0
1°	1997.7
2°	1988.6
3°	1970.4
4°	1948.9
5°	1915.8
6°	1874.4
7°	1828.1
8°	1775.9
9°	1716.4
10°	1650.2
11°	1576.5
12°	1499.5
13°	1413.5
14°	1331.5
15°	1239.7
17.5°	1017.1
20°	806.9
22.5°	620.7
25°	470.9
27.5°	350.9
30°	258.2
32.5°	189.5
35°	136.5
37.5°	96.8
40°	67.9
42.5°	47.2
45°	32.3
47.5°	21.5
50°	14.1
52.5°	10.8
55°	9.9
57.5°	9.1
60°	8.3
62.5°	7.4
65°	5.8
67.5°	5.0
70°	5.0
72.5°	4.1
75°	3.3
77.5°	2.5
80°	2.5
82.5°	1.7
85°	0.8
87.5°	0.8



TEST NUMBER: P1252709

CATALOG NUMBER: P3AS20R359030D010 E3DL1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)