

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252728

Luminaire Tested: P3AS20R359030D010 E3PHLD1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1252728
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-20)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R359030D010 E3PHLD1MW
Description: 3in Adjustable LED luminaire with, R35 optic, 3000K CCT AND, 90CRI , E3PHLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1310.0 lumens
Efficiency: N/A
Efficacy: 45.5 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.92
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1252728
CATALOG NUMBER: P3AS20R359030D010 E3PHLD1MW

Luminous Intensity Polar Plot



— 0°-180° - - - 45°-225° ····· 90°-270°



TEST NUMBER: P1252728
 CATALOG NUMBER: P3AS20R359030D010 E3PHLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	100	
1	111	107	103	100	108	105	101	99	100	98	95	97	95	93	93	91	90	90	88	
2	103	96	90	85	100	94	89	84	90	86	82	87	84	81	84	81	79	79	77	
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	70	70	68	
4	88	78	71	65	86	77	70	65	75	68	64	72	67	63	70	66	62	62	60	
5	82	71	64	58	80	70	63	58	68	62	57	66	61	56	65	60	56	56	54	
6	77	65	58	52	75	65	57	52	63	56	51	61	55	51	60	55	51	51	49	
7	72	60	53	47	71	60	52	47	58	52	47	57	51	46	55	50	46	46	44	
8	68	56	48	43	66	55	48	43	54	47	43	53	47	43	52	46	42	42	41	
9	64	52	45	40	63	51	44	40	50	44	39	49	44	39	48	43	39	39	38	
10	60	49	42	37	59	48	41	37	47	41	37	46	41	36	45	40	36	36	35	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	215027	215027	215027
5°	211005	210631	211005
10°	198393	198015	198393
15°	179615	179615	180001
20°	158984	158984	158984
25°	138250	137863	137863
30°	119867	119006	119436
35°	103195	102740	103195
40°	89539	89053	89539
45°	78644	78117	78117
50°	69797	69217	69217
55°	61398	61398	61398
60°	55610	54864	55610
65°	50018	50018	50018
70°	44431	44431	44431
75°	40074	38634	40074
80°	34222	34222	34222
85°	21386	21386	21386

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 78644 cd/sqm



TEST NUMBER: P1252728
 CATALOG NUMBER: P3AS20R359030D010 E3PHLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.2	6.8
10°-20°	220.7	16.8
20°-30°	262.2	20.0
30°-40°	241.0	18.4
40°-50°	195.7	14.9
50°-60°	144.8	11.1
60°-70°	95.7	7.3
70°-80°	49.6	3.8
80°-90°	11.2	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	572.1	43.7
0°-40°	813.1	62.1
0°-60°	1153.6	88.1
0°-90°	1310.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1310.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	981	981	981	981	981	
5°	959	957	957	957	959	89
15°	791	791	791	791	793	221
25°	571	570	570	571	570	263
35°	386	384	384	386	386	241
45°	254	252	252	252	252	196
55°	161	161	161	161	161	145
65°	96	96	96	96	96	96
75°	47	47	46	47	47	50
85°	8	8	8	8	8	11
90°	0	0	0	0	0	



TEST NUMBER: P1252728
 CATALOG NUMBER: P3AS20R359030D010 E3PHLD1MW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	980.6	980.6	980.6	980.6	980.6
1°	980.6	978.9	978.9	978.9	980.6
2°	977.2	977.2	977.2	977.2	977.2
3°	973.8	972.1	972.1	972.1	972.1
4°	967.1	965.4	965.4	965.4	965.4
5°	958.6	956.9	956.9	956.9	958.6
6°	948.5	946.8	945.1	945.1	946.8
7°	938.3	934.9	934.9	934.9	934.9
8°	923.1	921.4	921.4	921.4	921.4
9°	907.9	904.5	906.2	906.2	906.2
10°	891.0	889.3	889.3	889.3	891.0
11°	874.1	872.4	872.4	870.7	872.4
12°	853.8	853.8	853.8	853.8	853.8
13°	835.2	833.5	833.5	833.5	835.2
14°	814.9	813.2	813.2	813.2	813.2
15°	791.2	791.2	791.2	791.2	792.9
17.5°	737.1	735.4	737.1	737.1	738.8
20°	681.3	679.6	681.3	681.3	681.3
22.5°	625.5	625.5	623.9	625.5	627.2
25°	571.4	569.8	569.8	571.4	569.8
27.5°	520.7	519.0	519.0	519.0	519.0
30°	473.4	470.0	470.0	471.7	471.7
32.5°	424.4	424.4	426.0	424.4	424.4
35°	385.5	383.8	383.8	385.5	385.5
37.5°	346.6	344.9	344.9	346.6	346.6
40°	312.8	312.8	311.1	312.8	312.8
42.5°	280.7	280.7	280.7	280.7	280.7
45°	253.6	251.9	251.9	251.9	251.9
47.5°	226.5	226.5	226.5	224.9	226.5
50°	204.6	202.9	202.9	202.9	202.9
52.5°	180.9	180.9	180.9	180.9	180.9
55°	160.6	160.6	160.6	160.6	160.6
57.5°	143.7	142.0	142.0	142.0	142.0
60°	126.8	126.8	125.1	126.8	126.8
62.5°	109.9	109.9	109.9	109.9	109.9
65°	96.4	96.4	96.4	96.4	96.4
67.5°	82.8	82.8	82.8	82.8	82.8
70°	69.3	69.3	69.3	69.3	69.3
72.5°	59.2	57.5	57.5	57.5	57.5
75°	47.3	47.3	45.6	47.3	47.3
77.5°	35.5	35.5	35.5	35.5	35.5
80°	27.1	27.1	27.1	25.4	27.1
82.5°	16.9	16.9	16.9	16.9	16.9
85°	8.5	8.5	8.5	8.5	8.5
87.5°	1.7	1.7	1.7	3.4	3.4



TEST NUMBER: P1252728
CATALOG NUMBER: P3AS20R359030D010 E3PHLD1MW

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)