

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251895

Luminaire Tested: P3AS13R209030DE010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1251895
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R209030DE010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R20 optic, 3000K CCT AND, 90CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1227.0 lumens
Efficiency: N/A
Efficacy: 84.0 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1251895

CATALOG NUMBER: P3AS13R209030DE010 E3CD1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1251895

CATALOG NUMBER: P3AS13R209030DE010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	116	114	112	110	113	112	110	109	108	106	105		104	103	102		101
2	112	109	107	104	110	108	105	103	104	103	101		102	100	99		99
3	109	105	102	100	108	104	101	99	102	99	97		99	98	96		97
4	107	102	99	96	105	101	98	96	99	97	95		97	95	93		96
5	104	99	96	93	103	98	95	93	97	94	92		95	93	91		94
6	102	97	93	91	101	96	93	90	95	92	90		94	91	89		93
7	100	94	91	88	99	94	91	88	93	90	88		92	89	87		91
8	98	92	89	86	97	92	89	86	91	88	86		90	88	86		89
9	96	90	87	85	95	90	87	85	89	86	84		89	86	84		88
10	94	89	85	83	93	88	85	83	88	85	83		87	84	83		86

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1905681
5°	1654057
10°	1022025
15°	354985
20°	109023
25°	38543
30°	14255
35°	5729
40°	3063
45°	1209
50°	648
55°	726
60°	833
65°	519
70°	641
75°	847
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1209 cd/sqm

TEST NUMBER: P1251895

CATALOG NUMBER: P3AS13R209030DE010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	623.6	50.8
10°-20°	494.8	40.3
20°-30°	85.7	7.0
30°-40°	15.6	1.3
40°-50°	3.6	0.3
50°-60°	1.7	0.1
60°-70°	1.1	0.1
70°-80°	0.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1204.1	98.1
0°-40°	1219.7	99.4
0°-60°	1225.0	99.8
0°-90°	1227.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1227.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8691	
5°	7514	624
15°	1564	495
25°	159	86
35°	21	16
45°	4	4
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1251895

CATALOG NUMBER: P3AS13R209030DE010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	8690.6
1°	8648.8
2°	8483.7
3°	8218.5
4°	7907.7
5°	7514.4
6°	7063.7
7°	6539.3
8°	5942.0
9°	5270.9
10°	4590.0
12.5°	2895.2
15°	1563.7
17.5°	835.3
20°	467.2
22.5°	267.1
25°	159.3
27.5°	97.1
30°	56.3
32.5°	33.0
35°	21.4
37.5°	14.6
40°	10.7
42.5°	6.8
45°	3.9
47.5°	1.9
50°	1.9
52.5°	1.9
55°	1.9
57.5°	1.9
60°	1.9
62.5°	1.0
65°	1.0
67.5°	1.0
70°	1.0
72.5°	1.0
75°	1.0
77.5°	1.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)