

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251917

Luminaire Tested: P3AS13R259030DE010 E3CB1MB

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1251917
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R259030DE010 E3CB1MB
Description: 3in Adjustable LED luminaire with, R25 optic, 3000K CCT AND, 90CRI , E3CB1MB TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1237.0 lumens
Efficiency: N/A
Efficacy: 84.7 lumens/watt
Spacing Criteria (0/90/45): 0.45 / 0.45 / 0.41
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1251917

CATALOG NUMBER: P3AS13R259030DE010 E3CB1MB

Luminous Intensity Polar Plot



TEST NUMBER: P1251917

CATALOG NUMBER: P3AS13R259030DE010 E3CB1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	99
1	115	113	111	110	113	111	109	108	107	106	105	103	103	102	100	99	99	97	96	96
2	112	108	105	103	110	107	104	102	104	102	100	101	99	98	98	97	96	94	93	93
3	108	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92	91	91
4	105	100	97	94	104	99	96	93	97	95	92	96	93	91	94	92	90	89	88	88
5	103	97	93	90	101	96	93	90	95	92	89	93	91	89	92	90	88	87	86	86
6	100	94	90	87	99	93	90	87	92	89	87	91	88	86	90	87	86	85	84	84
7	97	91	88	85	96	91	87	85	90	87	84	89	86	84	88	85	83	83	82	82
8	95	89	85	83	94	89	85	82	88	84	82	87	84	82	86	83	81	81	80	80
9	93	87	83	80	92	86	83	80	86	82	80	85	82	80	84	82	80	79	78	78
10	91	85	81	78	90	84	81	78	84	80	78	83	80	78	82	80	78	77	76	76

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1322526
5°	1226609
10°	951263
15°	476983
20°	156697
25°	62302
30°	23371
35°	6773
40°	3063
45°	1209
50°	989
55°	726
60°	833
65°	986
70°	641
75°	847
80°	1263
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 80°

Luminance: 1263 cd/sqm

TEST NUMBER: P1251917

CATALOG NUMBER: P3AS13R259030DE010 E3CB1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	490.1	39.6
10°-20°	584.8	47.3
20°-30°	131.8	10.7
30°-40°	21.4	1.7
40°-50°	3.9	0.3
50°-60°	2.0	0.2
60°-70°	1.8	0.1
70°-80°	1.1	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1206.7	97.6
0°-40°	1228.1	99.3
0°-60°	1234.0	99.8
0°-90°	1237.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1237.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6031	
5°	5572	490
15°	2101	585
25°	258	132
35°	25	21
45°	4	4
55°	2	2
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1251917

CATALOG NUMBER: P3AS13R259030DE010 E3CB1MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	6031.2
1°	6021.5
2°	5972.9
3°	5883.5
4°	5748.4
5°	5572.5
6°	5362.6
7°	5135.2
8°	4874.7
9°	4590.0
10°	4272.2
11°	3905.8
12°	3484.0
13°	3042.8
14°	2569.5
15°	2101.1
17.5°	1197.3
20°	671.5
22.5°	405.3
25°	257.5
27.5°	158.4
30°	92.3
32.5°	48.6
35°	25.3
37.5°	16.5
40°	10.7
42.5°	6.8
45°	3.9
47.5°	2.9
50°	2.9
52.5°	2.9
55°	1.9
57.5°	1.9
60°	1.9
62.5°	1.9
65°	1.9
67.5°	1.9
70°	1.0
72.5°	1.0
75°	1.0
77.5°	1.0
80°	1.0
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1251917

CATALOG NUMBER: P3AS13R259030DE010 E3CB1MB

CANDELA DISTRIBUTION (continued):



(END OF REPORT)