

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252766

Luminaire Tested: P3AS20R459030D010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1252766
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R459030D010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R45 optic, 3000K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 926.0 lumens
Efficiency: N/A
Efficacy: 32.2 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1252766

CATALOG NUMBER: P3AS20R459030D010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1252766

CATALOG NUMBER: P3AS20R459030D010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93
3	104	98	93	89	102	96	92	88	94	90	87		91	88	86		89
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85
5	94	87	81	77	93	86	81	77	84	80	76		82	79	76		81
6	90	82	76	73	89	81	76	72	80	75	72		78	74	71		77
7	86	78	72	68	85	77	72	68	76	71	68		75	71	67		74
8	83	74	68	65	82	73	68	64	72	68	64		71	67	64		70
9	79	70	65	61	78	70	65	61	69	64	61		68	64	61		67
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	347735
5°	339599
10°	312174
15°	264519
20°	205235
25°	143452
30°	90368
35°	53190
40°	30114
45°	14637
50°	5083
55°	4129
60°	3991
65°	3891
70°	3719
75°	3474
80°	3157
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 14637 cd/sqm

TEST NUMBER: P1252766

CATALOG NUMBER: P3AS20R459030D010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	142.8	15.4
10°-20°	320.0	34.6
20°-30°	271.7	29.3
30°-40°	129.6	14.0
40°-50°	39.0	4.2
50°-60°	9.9	1.1
60°-70°	7.4	0.8
70°-80°	4.4	0.5
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	734.5	79.3
0°-40°	864.1	93.3
0°-60°	913.0	98.6
0°-90°	926.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	926.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1586	
5°	1543	143
15°	1165	320
25°	593	272
35°	199	130
45°	47	39
55°	11	10
65°	8	7
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1252766

CATALOG NUMBER: P3AS20R459030D010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1585.8
2.5°	1575.9
5°	1542.8
7.5°	1485.6
10°	1402.0
12.5°	1291.0
15°	1165.2
17.5°	1025.2
20°	879.5
22.5°	731.2
25°	592.9
27.5°	467.1
30°	356.9
32.5°	268.3
35°	198.7
37.5°	146.6
40°	105.2
42.5°	72.9
45°	47.2
47.5°	26.5
50°	14.9
52.5°	11.6
55°	10.8
57.5°	9.9
60°	9.1
62.5°	8.3
65°	7.5
67.5°	6.6
70°	5.8
72.5°	5.0
75°	4.1
77.5°	3.3
80°	2.5
82.5°	1.7
85°	0.8
87.5°	0.8
90°	0.0

(END OF REPORT)