

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251928

Luminaire Tested: P3AS13R259030DE010 E3DL1GPH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1251928  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R259030DE010 E3DL1GPH  
Description: 3in Adjustable LED luminaire with, R25 optic, 3000K CCT AND, 90CRI , E3DL1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 499.0 lumens  
Efficiency: N/A  
Efficacy: 34.2 lumens/watt  
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 14.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1251928  
CATALOG NUMBER: P3AS13R259030DE010 E3DL1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P1251928  
 CATALOG NUMBER: P3AS13R259030DE010 E3DL1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20					
RC	80				70				50				30				10			0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	97	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	93	92	95
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90	91	89	87	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86	88	85	83	86
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	82	86	83	81	82
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78	85	82	79	78
6	94	86	81	78	92	86	81	78	84	80	77	83	79	77	82	78	76	75	82	78	76	75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	75	73	72	79	75	73	72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69	76	73	70	69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	67	66	73	70	67	66
10	81	73	69	65	80	73	68	65	72	68	65	72	68	65	71	67	65	64	71	67	65	64

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	320084
5°	298634
10°	239230
15°	162385
20°	98265
25°	57463
30°	32714
35°	17989
40°	9561
45°	5024
50°	2934
55°	2179
60°	1886
65°	1972
70°	1859
75°	1610
80°	1263
85°	1258

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 5024 cd/sqm



TEST NUMBER: P1251928  
 CATALOG NUMBER: P3AS13R259030DE010 E3DL1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	120.4	24.1
10°-20°	196.7	39.4
20°-30°	112.4	22.5
30°-40°	44.3	8.9
40°-50°	13.6	2.7
50°-60°	5.4	1.1
60°-70°	3.6	0.7
70°-80°	2.0	0.4
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	429.4	86.1
0°-40°	473.8	94.9
0°-60°	492.7	98.7
0°-90°	499.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	499.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1460	
5°	1357	120
15°	715	197
25°	238	112
35°	67	44
45°	16	14
55°	6	5
65°	4	4
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1251928  
CATALOG NUMBER: P3AS13R259030DE010 E3DL1GPH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1459.7
1°	1456.9
2°	1444.9
3°	1424.0
4°	1394.9
5°	1356.7
6°	1311.9
7°	1261.3
8°	1202.7
9°	1142.6
10°	1074.4
11°	1007.2
12°	933.3
13°	860.3
14°	785.4
15°	715.3
17.5°	554.6
20°	421.1
22.5°	316.2
25°	237.5
27.5°	176.0
30°	129.2
32.5°	93.5
35°	67.2
37.5°	47.7
40°	33.4
42.5°	22.9
45°	16.2
47.5°	11.4
50°	8.6
52.5°	6.7
55°	5.7
57.5°	5.2
60°	4.3
62.5°	3.8
65°	3.8
67.5°	3.3
70°	2.9
72.5°	2.4
75°	1.9
77.5°	1.4
80°	1.0
82.5°	1.0
85°	0.5
87.5°	0.5



TEST NUMBER: P1251928  
CATALOG NUMBER: P3AS13R259030DE010 E3DL1GPH

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)