

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252778

Luminaire Tested: P3AS20R459030D010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1252778
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R459030D010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R45 optic, 3000K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 597.0 lumens
Efficiency: N/A
Efficacy: 20.7 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1252778

CATALOG NUMBER: P3AS20R459030D010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1252778

CATALOG NUMBER: P3AS20R459030D010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		86
3	102	95	90	85	100	93	89	85	91	87	83		88	85	82		79
4	96	88	83	78	94	87	82	78	85	81	77		83	79	76		74
5	91	83	77	72	90	82	76	72	80	75	71		78	74	71		69
6	87	78	72	67	85	77	71	67	75	70	66		74	69	66		64
7	83	73	67	63	81	72	67	63	71	66	62		70	65	62		60
8	79	69	63	59	77	68	63	59	67	62	58		66	62	58		56
9	75	65	59	55	74	65	59	55	64	59	55		63	58	55		53
10	72	62	56	52	71	61	56	52	61	55	52		60	55	52		50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	177815
5°	173761
10°	160295
15°	139388
20°	114507
25°	89086
30°	65782
35°	46284
40°	28911
45°	15661
50°	8460
55°	7264
60°	6535
65°	5604
70°	4744
75°	4914
80°	4167
85°	4277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15661 cd/sqm

TEST NUMBER: P1252778

CATALOG NUMBER: P3AS20R459030D010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.1	12.2
10°-20°	169.7	28.4
20°-30°	168.5	28.2
30°-40°	108.5	18.2
40°-50°	41.8	7.0
50°-60°	17.0	2.8
60°-70°	10.7	1.8
70°-80°	5.8	1.0
80°-90°	1.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	411.4	68.9
0°-40°	519.9	87.1
0°-60°	578.7	96.9
0°-90°	597.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	597.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	811	
5°	789	73
15°	614	170
25°	368	169
35°	173	109
45°	50	42
55°	19	17
65°	11	11
75°	6	6
85°	2	2
90°	0	

TEST NUMBER: P1252778

CATALOG NUMBER: P3AS20R459030D010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	810.9
2.5°	806.8
5°	789.4
7.5°	759.6
10°	719.9
12.5°	670.3
15°	614.0
17.5°	552.8
20°	490.7
22.5°	427.8
25°	368.2
27.5°	312.0
30°	259.8
32.5°	214.3
35°	172.9
37.5°	135.7
40°	101.0
42.5°	72.8
45°	50.5
47.5°	33.9
50°	24.8
52.5°	20.7
55°	19.0
57.5°	16.5
60°	14.9
62.5°	12.4
65°	10.8
67.5°	9.1
70°	7.4
72.5°	6.6
75°	5.8
77.5°	4.1
80°	3.3
82.5°	2.5
85°	1.7
87.5°	0.8
90°	0.0

(END OF REPORT)