

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252798

Luminaire Tested: P3AS20R509030D010 E3DL1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1252798
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R509030D010 E3DL1MW
Description: 3in Adjustable LED luminaire with, R50 optic, 3000K CCT AND, 90CRI , E3DL1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1901.0 lumens
Efficiency: N/A
Efficacy: 66.0 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1252798

CATALOG NUMBER: P3AS20R509030D010 E3DL1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1252798

CATALOG NUMBER: P3AS20R509030D010 E3DL1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10			0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102			100
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95			94
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89			87
3	103	97	92	88	101	95	91	87	93	89	86	90	87	84	88	85	83			82
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	80	78			76
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73			72
6	89	80	75	71	88	80	74	70	78	73	70	77	73	69	75	72	69			67
7	85	76	70	66	84	75	70	66	74	69	66	73	69	65	72	68	65			64
8	81	72	66	62	80	71	66	62	70	65	62	69	65	62	68	64	61			60
9	78	68	63	59	76	68	62	59	67	62	59	66	62	58	65	61	58			57
10	74	65	59	56	73	65	59	56	64	59	55	63	58	55	62	58	55			54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	605237
5°	593043
10°	555501
15°	497279
20°	418473
25°	319397
30°	207576
35°	123058
40°	71133
45°	35632
50°	13270
55°	10322
60°	9648
65°	8769
70°	8655
75°	8557
80°	8587
85°	8554

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 35632 cd/sqm

TEST NUMBER: P1252798

CATALOG NUMBER: P3AS20R509030D010 E3DL1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	250.7	13.2
10°-20°	605.8	31.9
20°-30°	594.3	31.3
30°-40°	299.4	15.7
40°-50°	94.6	5.0
50°-60°	24.5	1.3
60°-70°	17.3	0.9
70°-80°	10.7	0.6
80°-90°	3.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1450.7	76.3
0°-40°	1750.1	92.1
0°-60°	1869.3	98.3
0°-90°	1901.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1901.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2760	
5°	2694	251
15°	2190	606
25°	1320	594
35°	460	299
45°	115	95
55°	27	25
65°	17	17
75°	10	11
85°	3	4
90°	0	

TEST NUMBER: P1252798

CATALOG NUMBER: P3AS20R509030D010 E3DL1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	2760.1
2.5°	2743.2
5°	2694.2
7.5°	2606.3
10°	2494.8
12.5°	2351.1
15°	2190.5
17.5°	2004.6
20°	1793.3
22.5°	1565.1
25°	1320.1
27.5°	1059.8
30°	819.8
32.5°	616.9
35°	459.7
37.5°	339.7
40°	248.5
42.5°	175.8
45°	114.9
47.5°	65.9
50°	38.9
52.5°	28.7
55°	27.0
57.5°	23.7
60°	22.0
62.5°	20.3
65°	16.9
67.5°	15.2
70°	13.5
72.5°	11.8
75°	10.1
77.5°	8.5
80°	6.8
82.5°	5.1
85°	3.4
87.5°	1.7
90°	0.0

(END OF REPORT)