

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252824

Luminaire Tested: P3AS20R559030D010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1252824
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R559030D010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R55 optic, 3000K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 903.0 lumens
Efficiency: N/A
Efficacy: 31.4 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1252824

CATALOG NUMBER: P3AS20R559030D010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1252824

CATALOG NUMBER: P3AS20R559030D010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	84		87
4	97	90	84	80	95	89	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	86	78	73	68	77	72	68		75	71	68		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	64	60	78	70	64	60	69	63	60		67	63	60		67
9	76	66	61	57	75	66	60	56	65	60	56		64	59	56		63
10	73	63	57	53	72	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	247963
5°	245432
10°	237025
15°	219093
20°	189063
25°	149331
30°	105915
35°	68288
40°	41020
45°	23134
50°	12418
55°	4435
60°	3991
65°	3891
70°	3719
75°	3474
80°	3157
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 23134 cd/sqm

TEST NUMBER: P1252824

CATALOG NUMBER: P3AS20R559030D010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	104.9	11.6
10°-20°	266.9	29.6
20°-30°	279.7	31.0
30°-40°	163.1	18.1
40°-50°	61.0	6.8
50°-60°	14.4	1.6
60°-70°	7.4	0.8
70°-80°	4.4	0.5
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	651.4	72.1
0°-40°	814.6	90.2
0°-60°	890.0	98.6
0°-90°	903.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	903.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1131	
5°	1115	105
15°	965	267
25°	617	280
35°	255	163
45°	75	61
55°	12	14
65°	8	7
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1252824

CATALOG NUMBER: P3AS20R559030D010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1130.8
2.5°	1127.5
5°	1115.0
7.5°	1095.2
10°	1064.5
12.5°	1021.4
15°	965.1
17.5°	893.9
20°	810.2
22.5°	716.6
25°	617.2
27.5°	515.3
30°	418.3
32.5°	330.5
35°	255.1
37.5°	193.8
40°	143.3
42.5°	102.7
45°	74.6
47.5°	53.8
50°	36.4
52.5°	20.7
55°	11.6
57.5°	9.9
60°	9.1
62.5°	8.3
65°	7.5
67.5°	6.6
70°	5.8
72.5°	5.0
75°	4.1
77.5°	3.3
80°	2.5
82.5°	1.7
85°	0.8
87.5°	0.8
90°	0.0

(END OF REPORT)