

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252874

Luminaire Tested: P3AS20R659030D010 E3CD1MB

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1252874
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-44)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R659030D010 E3CD1MB
Description: 3in Adjustable LED luminaire with, R65 optic, 3000K CCT AND, 90CRI , E3CD1MB TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2090.1 lumens
Efficiency: N/A
Efficacy: 72.6 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.9
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1252874

CATALOG NUMBER: P3AS20R659030D010 E3CD1MB

Luminous Intensity Polar Plot



TEST NUMBER: P1252874

CATALOG NUMBER: P3AS20R659030D010 E3CD1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94		
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87		
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81		
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77	75		
5	93	84	78	74	91	83	78	74	82	77	73	80	76	73	78	75	72	70		
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66		
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62		
8	80	70	64	60	78	69	64	60	68	63	60	67	63	59	66	62	59	58		
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54		
10	72	63	57	53	71	62	57	53	61	56	53	60	56	53	60	55	52	51		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	510749
5°	480694
10°	474585
15°	466223
20°	440198
25°	408556
30°	317568
35°	183717
40°	74024
45°	34081
50°	13270
55°	5161
60°	4429
65°	4410
70°	4360
75°	4321
80°	4293
85°	4277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 34081 cd/sqm

TEST NUMBER: P1252874

CATALOG NUMBER: P3AS20R659030D010 E3CD1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	207.6	9.9
10°-20°	573.5	27.4
20°-30°	750.7	35.9
30°-40°	434.8	20.8
40°-50°	93.1	4.5
50°-60°	15.1	0.7
60°-70°	8.4	0.4
70°-80°	4.9	0.2
80°-90°	1.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1531.8	73.3
0°-40°	1966.7	94.1
0°-60°	2074.9	99.3
0°-90°	2090.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2090.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2329	
5°	2184	208
15°	2054	573
25°	1689	751
35°	686	435
45°	110	93
55°	14	15
65°	8	8
75°	5	5
85°	2	2
90°	0	

TEST NUMBER: P1252874

CATALOG NUMBER: P3AS20R659030D010 E3CD1MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	2329.2
2.5°	2263.3
5°	2183.8
7.5°	2151.7
10°	2131.4
12.5°	2102.7
15°	2053.7
17.5°	1977.6
20°	1886.4
22.5°	1800.1
25°	1688.6
27.5°	1501.0
30°	1254.2
32.5°	971.9
35°	686.3
37.5°	434.4
40°	258.6
42.5°	162.3
45°	109.9
47.5°	71.0
50°	38.9
52.5°	18.6
55°	13.5
57.5°	11.8
60°	10.1
62.5°	10.1
65°	8.5
67.5°	6.8
70°	6.8
72.5°	5.1
75°	5.1
77.5°	3.4
80°	3.4
82.5°	1.7
85°	1.7
87.5°	1.7
90°	0.0

(END OF REPORT)