

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252036

Luminaire Tested: P3AS13R409030DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1252036
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R409030DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R40 optic, 3000K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1132.0 lumens
Efficiency: N/A
Efficacy: 77.5 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1252036

CATALOG NUMBER: P3AS13R409030DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1252036

CATALOG NUMBER: P3AS13R409030DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	112	109	107	105	105	104	102		102	100	99		98
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94
3	104	99	94	91	102	97	93	90	95	91	88		92	89	87		90
4	100	93	88	85	98	92	88	84	90	86	83		88	85	82		86
5	96	88	83	79	94	88	83	79	86	82	78		84	81	78		83
6	92	84	79	75	91	83	78	75	82	78	74		81	77	74		79
7	88	80	75	71	87	79	74	71	78	74	71		77	73	70		76
8	85	76	71	68	84	76	71	67	75	70	67		74	70	67		73
9	82	73	68	64	81	73	68	64	72	67	64		71	67	64		70
10	78	70	65	62	78	70	65	61	69	64	61		68	64	61		67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	500903
5°	486351
10°	441341
15°	364610
20°	263013
25°	162687
30°	88064
35°	45508
40°	24761
45°	13862
50°	6959
55°	5199
60°	4693
65°	4514
70°	4360
75°	4151
80°	3662
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13862 cd/sqm

TEST NUMBER: P1252036

CATALOG NUMBER: P3AS13R409030DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	203.7	18.0
10°-20°	437.3	38.6
20°-30°	312.1	27.6
30°-40°	114.9	10.1
40°-50°	36.2	3.2
50°-60°	12.6	1.1
60°-70°	8.6	0.8
70°-80°	5.1	0.5
80°-90°	1.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	953.1	84.2
0°-40°	1068.0	94.3
0°-60°	1116.8	98.7
0°-90°	1132.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1132.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2284	
5°	2210	204
15°	1606	437
25°	672	312
35°	170	115
45°	45	36
55°	14	13
65°	9	9
75°	5	5
85°	1	1
90°	0	

TEST NUMBER: P1252036

CATALOG NUMBER: P3AS13R409030DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2284.3
2.5°	2266.8
5°	2209.5
7.5°	2114.3
10°	1982.1
12.5°	1814.0
15°	1606.1
17.5°	1372.9
20°	1127.1
22.5°	885.2
25°	672.4
27.5°	493.6
30°	347.8
32.5°	243.9
35°	170.0
37.5°	120.5
40°	86.5
42.5°	62.2
45°	44.7
47.5°	30.1
50°	20.4
52.5°	14.6
55°	13.6
57.5°	12.6
60°	10.7
62.5°	9.7
65°	8.7
67.5°	7.8
70°	6.8
72.5°	5.8
75°	4.9
77.5°	3.9
80°	2.9
82.5°	1.9
85°	1.0
87.5°	1.0
90°	0.0

(END OF REPORT)