

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252904

Luminaire Tested: P3AS20R709030D010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1252904
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-48)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R709030D010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R70 optic, 3000K CCT AND, 90CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2114.0 lumens
Efficiency: N/A
Efficacy: 73.4 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.03
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1252904

CATALOG NUMBER: P3AS20R709030D010 E3CD1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1252904

CATALOG NUMBER: P3AS20R709030D010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85
4	95	87	81	77	94	86	81	76	84	79	75		82	78	75		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	75	69	64	83	75	69	64	73	68	64		72	67	63		70
7	80	70	64	59	79	70	64	59	68	63	59		67	62	59		66
8	76	66	59	55	75	65	59	55	64	58	55		63	58	54		62
9	72	62	55	51	71	61	55	51	60	55	51		59	54	50		58
10	68	58	52	47	67	57	51	47	56	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	419791
5°	400549
10°	381111
15°	370922
20°	357218
25°	338076
30°	314453
35°	264159
40°	170262
45°	79109
50°	20741
55°	5161
60°	5175
65°	4358
70°	4360
75°	4321
80°	4293
85°	4277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 79109 cd/sqm

TEST NUMBER: P1252904

CATALOG NUMBER: P3AS20R709030D010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	170.3	8.1
10°-20°	459.1	21.7
20°-30°	641.4	30.3
30°-40°	594.7	28.1
40°-50°	213.2	10.1
50°-60°	18.1	0.9
60°-70°	9.0	0.4
70°-80°	5.8	0.3
80°-90°	2.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1270.9	60.1
0°-40°	1865.6	88.3
0°-60°	2096.9	99.2
0°-90°	2114.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2114.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1914	
5°	1820	170
15°	1634	459
25°	1397	641
35°	987	595
45°	255	213
55°	14	18
65°	8	9
75°	5	6
85°	2	2
90°	0	

TEST NUMBER: P1252904

CATALOG NUMBER: P3AS20R709030D010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	1914.4
2.5°	1885.6
5°	1819.7
7.5°	1758.9
10°	1711.6
12.5°	1672.7
15°	1633.9
17.5°	1586.6
20°	1530.8
22.5°	1466.6
25°	1397.3
27.5°	1326.4
30°	1241.9
32.5°	1133.7
35°	986.8
37.5°	799.2
40°	594.8
42.5°	405.5
45°	255.1
47.5°	141.9
50°	60.8
52.5°	20.3
55°	13.5
57.5°	11.8
60°	11.8
62.5°	10.1
65°	8.4
67.5°	8.4
70°	6.8
72.5°	6.8
75°	5.1
77.5°	5.1
80°	3.4
82.5°	3.4
85°	1.7
87.5°	1.7
90°	0.0

(END OF REPORT)