

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252045

Luminaire Tested: P3AS13R459030DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1252045
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R459030DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R45 optic, 3000K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 532.0 lumens
Efficiency: N/A
Efficacy: 36.4 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1252045
CATALOG NUMBER: P3AS13R459030DE010 E3DL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1252045
 CATALOG NUMBER: P3AS13R459030DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94				94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	91	90	88				88
3	104	98	93	89	102	96	92	88	94	90	87	91	88	86	89	86	84	83				83
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78				78
5	94	87	81	77	93	86	81	77	84	80	76	82	79	76	81	78	75	74				74
6	90	82	76	73	89	81	76	72	80	75	72	78	74	71	77	74	71	70				70
7	86	78	72	68	85	77	72	68	76	71	68	75	71	67	74	70	67	66				66
8	83	74	68	65	82	73	68	64	72	68	64	71	67	64	70	67	64	62				62
9	79	70	65	61	78	70	65	61	69	64	61	68	64	61	67	63	61	59				59
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57				57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	199787
5°	195113
10°	179355
15°	151965
20°	117914
25°	82408
30°	51932
35°	30570
40°	17290
45°	8404
50°	2934
55°	2370
60°	2281
65°	2231
70°	2116
75°	2033
80°	1768
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8404 cd/sqm



TEST NUMBER: P1252045
 CATALOG NUMBER: P3AS13R459030DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.0	15.4
10°-20°	183.8	34.6
20°-30°	156.1	29.3
30°-40°	74.5	14.0
40°-50°	22.4	4.2
50°-60°	5.7	1.1
60°-70°	4.2	0.8
70°-80°	2.5	0.5
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	422.0	79.3
0°-40°	496.4	93.3
0°-60°	524.5	98.6
0°-90°	532.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	532.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	911	
5°	886	82
15°	669	184
25°	341	156
35°	114	74
45°	27	22
55°	6	6
65°	4	4
75°	2	3
85°	0	1
90°	0	



TEST NUMBER: P1252045
CATALOG NUMBER: P3AS13R459030DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	911.1
2.5°	905.4
5°	886.4
7.5°	853.5
10°	805.5
12.5°	741.7
15°	669.4
17.5°	589.0
20°	505.3
22.5°	420.1
25°	340.6
27.5°	268.3
30°	205.1
32.5°	154.1
35°	114.2
37.5°	84.2
40°	60.4
42.5°	41.9
45°	27.1
47.5°	15.2
50°	8.6
52.5°	6.7
55°	6.2
57.5°	5.7
60°	5.2
62.5°	4.8
65°	4.3
67.5°	3.8
70°	3.3
72.5°	2.9
75°	2.4
77.5°	1.9
80°	1.4
82.5°	1.0
85°	0.5
87.5°	0.5
90°	0.0

(END OF REPORT)