

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252967

Luminaire Tested: P3AS24R209030D010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1252967
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS24R209030D010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R20 optic, 3000K CCT AND, 90CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2393.9 lumens
Efficiency: N/A
Efficacy: 83.1 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1252967

CATALOG NUMBER: P3AS24R209030D010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1252967

CATALOG NUMBER: P3AS24R209030D010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	114	112	110	113	111	110	108	107	106	105		104	103	102		100
2	112	109	106	104	110	107	105	103	104	102	101		101	100	98		99
3	109	105	102	99	107	104	101	98	101	99	97		99	97	95		97
4	106	101	98	95	105	100	97	95	99	96	94		97	95	93		95
5	104	98	95	92	102	98	94	92	96	93	91		95	92	90		93
6	101	96	92	89	100	95	92	89	94	91	89		93	90	88		92
7	99	93	90	87	98	93	89	87	92	89	86		91	88	86		90
8	97	91	87	85	96	91	87	85	90	87	85		89	86	84		88
9	95	89	85	83	94	89	85	83	88	85	83		87	84	83		87
10	93	87	84	81	92	87	83	81	86	83	81		86	83	81		85

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3631507
5°	3057553
10°	1909717
15°	713966
20°	245068
25°	102127
30°	48109
35°	21549
40°	10191
45°	5210
50°	1910
55°	344
60°	395
65°	467
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 5210 cd/sqm

TEST NUMBER: P1252967

CATALOG NUMBER: P3AS24R209030D010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1155.1	48.3
10°-20°	951.5	39.7
20°-30°	216.2	9.0
30°-40°	55.0	2.3
40°-50°	13.8	0.6
50°-60°	1.7	0.1
60°-70°	0.6	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2322.8	97.0
0°-40°	2377.8	99.3
0°-60°	2393.4	100.0
0°-90°	2393.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2393.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	16561	
5°	13890	###
15°	3145	951
25°	422	216
35°	80	55
45°	17	14
55°	1	2
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1252967

CATALOG NUMBER: P3AS24R209030D010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	16561.0
1°	16420.6
2°	16006.9
3°	15413.4
4°	14685.2
5°	13890.5
6°	13005.0
7°	12027.8
8°	10887.8
9°	9758.0
10°	8576.7
11°	7319.7
12°	6064.5
13°	5001.2
14°	3984.6
15°	3145.0
16°	2482.3
17°	1958.2
18°	1573.4
19°	1279.5
20°	1050.2
21°	878.0
22°	732.9
23°	609.3
24°	508.3
25°	422.1
27.5°	276.1
30°	190.0
32.5°	117.0
35°	80.5
37.5°	51.5
40°	35.6
42.5°	24.3
45°	16.8
47.5°	11.2
50°	5.6
52.5°	2.8
55°	0.9
57.5°	0.9
60°	0.9
62.5°	0.9
65°	0.9
67.5°	0.0
70°	0.0
72.5°	0.0

TEST NUMBER: P1252967

CATALOG NUMBER: P3AS24R209030D010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)