

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252085

Luminaire Tested: P3AS13R509030DE010 E3DLD1WMH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1252085  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R509030DE010 E3DLD1WMH  
Description: 3in Adjustable LED luminaire with, R50 optic, 3000K CCT AND, 90CRI , E3DLD1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 851.0 lumens  
Efficiency: N/A  
Efficacy: 58.3 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 14.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1252085  
CATALOG NUMBER: P3AS13R509030DE010 E3DLD1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P1252085

CATALOG NUMBER: P3AS13R509030DE010 E3DLD1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91			91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	83			83
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			75
4	93	85	78	73	91	83	77	73	81	76	72	79	75	71	77	73	70	69			69
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	64	63			63
6	83	73	66	61	81	72	65	61	70	65	60	69	64	60	67	63	59	58			58
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	53			53
8	74	63	57	52	73	63	56	52	61	56	52	60	55	51	59	55	51	50			50
9	70	59	53	48	69	59	52	48	58	52	48	57	52	48	56	51	48	46			46
10	66	56	49	45	65	55	49	45	54	49	45	54	48	45	53	48	45	43			43

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	172947
5°	170394
10°	162856
15°	150807
20°	135532
25°	119136
30°	101332
35°	82155
40°	61716
45°	39756
50°	18899
55°	14872
60°	14078
65°	13127
70°	11861
75°	10675
80°	9850
85°	9812

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 39756 cd/sqm



TEST NUMBER: P1252085

CATALOG NUMBER: P3AS13R509030DE010 E3DLD1WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	72.6	8.5
10°-20°	185.2	21.8
20°-30°	225.0	26.4
30°-40°	190.8	22.4
40°-50°	99.1	11.6
50°-60°	35.8	4.2
60°-70°	24.8	2.9
70°-80°	13.4	1.6
80°-90°	4.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	482.8	56.7
0°-40°	673.7	79.2
0°-60°	808.6	95.0
0°-90°	851.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	851.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	789	
5°	774	73
15°	664	185
25°	492	225
35°	307	191
45°	128	99
55°	39	36
65°	25	25
75°	13	13
85°	4	4
90°	0	



TEST NUMBER: P1252085  
CATALOG NUMBER: P3AS13R509030DE010 E3DLD1WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	788.7
2.5°	785.8
5°	774.1
7.5°	756.6
10°	731.4
12.5°	699.3
15°	664.3
17.5°	624.5
20°	580.8
22.5°	536.1
25°	492.4
27.5°	446.8
30°	400.2
32.5°	353.5
35°	306.9
37.5°	261.3
40°	215.6
42.5°	171.9
45°	128.2
47.5°	85.5
50°	55.4
52.5°	42.7
55°	38.9
57.5°	35.0
60°	32.1
62.5°	28.2
65°	25.3
67.5°	21.4
70°	18.5
72.5°	15.5
75°	12.6
77.5°	9.7
80°	7.8
82.5°	5.8
85°	3.9
87.5°	1.9
90°	0.0

(END OF REPORT)