

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252089

Luminaire Tested: P3AS13R509030DE010 E3DLP1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1252089
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R509030DE010 E3DLP1MW
Description: 3in Adjustable LED luminaire with, R50 optic, 3000K CCT AND, 90CRI , E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 717.0 lumens
Efficiency: N/A
Efficacy: 49.1 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1252089

CATALOG NUMBER: P3AS13R509030DE010 E3DLP1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1252089

CATALOG NUMBER: P3AS13R509030DE010 E3DLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93		
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85		
3	101	95	89	85	99	93	88	85	91	87	83	88	85	82	86	83	81	79		
4	96	88	82	78	94	87	82	78	85	80	77	83	79	76	81	78	75	73		
5	91	83	76	72	90	82	76	72	80	75	71	78	74	70	77	73	70	68		
6	87	77	71	67	85	77	71	67	75	70	66	74	69	66	72	68	65	64		
7	82	73	67	62	81	72	66	62	71	66	62	70	65	61	68	64	61	60		
8	78	69	63	58	77	68	62	58	67	62	58	66	61	58	65	61	57	56		
9	75	65	59	55	74	64	59	55	63	58	55	63	58	54	62	57	54	53		
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	208536
5°	202927
10°	187126
15°	164564
20°	137679
25°	109168
30°	80114
35°	55064
40°	35008
45°	19568
50°	10609
55°	8908
60°	7675
65°	7057
70°	6219
75°	5761
80°	4925
85°	4780

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 19568 cd/sqm

TEST NUMBER: P1252089

CATALOG NUMBER: P3AS13R509030DE010 E3DLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.4	11.9
10°-20°	200.8	28.0
20°-30°	205.4	28.6
30°-40°	130.2	18.2
40°-50°	51.8	7.2
50°-60°	21.0	2.9
60°-70°	13.4	1.9
70°-80°	6.9	1.0
80°-90°	2.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	491.5	68.5
0°-40°	621.7	86.7
0°-60°	694.6	96.9
0°-90°	717.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	717.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	951	
5°	922	85
15°	725	201
25°	451	205
35°	206	130
45°	63	52
55°	23	21
65°	14	13
75°	7	7
85°	2	2
90°	0	

TEST NUMBER: P1252089

CATALOG NUMBER: P3AS13R509030DE010 E3DLP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	951.0
2.5°	944.2
5°	921.9
7.5°	887.0
10°	840.4
12.5°	785.1
15°	724.9
17.5°	658.9
20°	590.0
22.5°	521.1
25°	451.2
27.5°	381.4
30°	316.4
32.5°	258.1
35°	205.7
37.5°	161.1
40°	122.3
42.5°	90.2
45°	63.1
47.5°	42.7
50°	31.1
52.5°	26.2
55°	23.3
57.5°	20.4
60°	17.5
62.5°	15.5
65°	13.6
67.5°	11.6
70°	9.7
72.5°	7.8
75°	6.8
77.5°	4.9
80°	3.9
82.5°	2.9
85°	1.9
87.5°	1.0
90°	0.0

(END OF REPORT)