

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252111

Luminaire Tested: P3AS13R559030DE010 E3DLD1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1252111
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-34)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R559030DE010 E3DLD1LI
Description: 3in Adjustable LED luminaire with, R55 optic, 3000K CCT AND, 90CRI , E3DLD1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 822.0 lumens
Efficiency: N/A
Efficacy: 56.3 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.97
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1252111
CATALOG NUMBER: P3AS13R559030DE010 E3DLD1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1252111
 CATALOG NUMBER: P3AS13R559030DE010 E3DLD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91			
2	105	100	95	91	103	98	93	90	94	91	88	91	88	86	89	86	84	82			
3	99	91	85	81	97	90	84	80	87	82	79	85	81	77	82	79	76	74			
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	73	69	68			
5	87	77	71	66	85	76	70	65	75	69	65	73	68	64	71	67	64	62			
6	82	72	65	60	80	71	64	60	69	64	59	68	63	59	66	62	58	57			
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52			
8	73	62	55	51	72	62	55	51	60	55	50	59	54	50	58	53	50	48			
9	69	58	51	47	68	58	51	47	57	51	47	56	50	46	55	50	46	45			
10	65	55	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	154549
5°	152586
10°	146557
15°	137095
20°	125054
25°	111587
30°	97585
35°	81084
40°	63920
45°	43353
50°	26507
55°	13725
60°	12762
65°	12089
70°	11220
75°	9913
80°	9850
85°	7296

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 43353 cd/sqm



TEST NUMBER: P1252111
 CATALOG NUMBER: P3AS13R559030DE010 E3DLD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.0	7.9
10°-20°	168.8	20.5
20°-30°	211.4	25.7
30°-40°	188.7	23.0
40°-50°	110.5	13.4
50°-60°	38.2	4.6
60°-70°	23.1	2.8
70°-80°	12.8	1.6
80°-90°	3.7	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	445.2	54.2
0°-40°	633.8	77.1
0°-60°	782.4	95.2
0°-90°	822.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	822.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	705	
5°	693	65
15°	604	169
25°	461	211
35°	303	189
45°	140	110
55°	36	38
65°	23	23
75°	12	13
85°	3	4
90°	0	



TEST NUMBER: P1252111
CATALOG NUMBER: P3AS13R559030DE010 E3DLD1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	704.8
2.5°	701.0
5°	693.2
7.5°	677.7
10°	658.2
12.5°	634.0
15°	603.9
17.5°	571.8
20°	535.9
22.5°	499.0
25°	461.2
27.5°	423.3
30°	385.4
32.5°	344.7
35°	302.9
37.5°	262.1
40°	223.3
42.5°	181.5
45°	139.8
47.5°	106.8
50°	77.7
52.5°	50.5
55°	35.9
57.5°	32.0
60°	29.1
62.5°	26.2
65°	23.3
67.5°	20.4
70°	17.5
72.5°	14.6
75°	11.7
77.5°	9.7
80°	7.8
82.5°	4.9
85°	2.9
87.5°	1.9
90°	0.0

(END OF REPORT)