

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252984

Luminaire Tested: P3AS24R259030D010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1252984
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS24R259030D010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R25 optic, 3000K CCT AND, 90CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2430.9 lumens
Efficiency: N/A
Efficacy: 84.4 lumens/watt
Spacing Criteria (0/90/45): 0.45 / 0.45 / 0.41
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1252984

CATALOG NUMBER: P3AS24R259030D010 E3CB1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1252984

CATALOG NUMBER: P3AS24R259030D010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	99
1	115	113	111	110	113	111	109	108	107	106	105	103	103	102	100	99	99	97	96	96
2	112	108	105	103	110	107	104	102	104	102	100	101	99	98	98	97	96	94	93	93
3	108	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92	91	91
4	105	100	97	94	104	99	96	93	97	95	92	96	93	91	94	92	90	89	88	88
5	103	97	93	90	101	96	93	90	95	92	89	93	91	89	92	90	88	87	86	86
6	100	94	90	87	99	93	90	87	92	89	87	91	88	86	90	87	86	85	84	84
7	97	91	88	85	96	91	87	85	90	87	84	89	86	84	88	85	83	83	82	82
8	95	89	85	83	94	89	85	82	88	84	82	87	84	82	86	83	81	81	80	80
9	93	87	83	80	92	86	83	80	86	82	80	85	82	80	84	82	80	79	78	78
10	91	85	81	78	90	84	81	78	84	80	78	83	80	78	82	80	78	77	76	76

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2599090
5°	2410581
10°	1869460
15°	937395
20°	307957
25°	122451
30°	45931
35°	13304
40°	6011
45°	2357
50°	1944
55°	1453
60°	1667
65°	1972
70°	1218
75°	1610
80°	2399
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 80°

Luminance: 2399 cd/sqm

TEST NUMBER: P1252984

CATALOG NUMBER: P3AS24R259030D010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	963.3	39.6
10°-20°	1149.2	47.3
20°-30°	259.1	10.7
30°-40°	42.0	1.7
40°-50°	7.6	0.3
50°-60°	4.0	0.2
60°-70°	3.5	0.1
70°-80°	2.0	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2371.5	97.6
0°-40°	2413.5	99.3
0°-60°	2425.1	99.8
0°-90°	2430.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2430.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11853	
5°	10951	963
15°	4129	1149
25°	506	259
35°	50	42
45°	8	8
55°	4	4
65°	4	4
75°	2	2
85°	0	0
90°	0	

TEST NUMBER: P1252984

CATALOG NUMBER: P3AS24R259030D010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	11852.8
1°	11833.7
2°	11738.2
3°	11562.5
4°	11297.0
5°	10951.3
6°	10538.8
7°	10091.9
8°	9580.0
9°	9020.4
10°	8395.9
11°	7675.9
12°	6847.0
13°	5979.9
14°	5049.8
15°	4129.2
17.5°	2353.0
20°	1319.7
22.5°	796.4
25°	506.1
27.5°	311.3
30°	181.4
32.5°	95.5
35°	49.7
37.5°	32.5
40°	21.0
42.5°	13.4
45°	7.6
47.5°	5.7
50°	5.7
52.5°	5.7
55°	3.8
57.5°	3.8
60°	3.8
62.5°	3.8
65°	3.8
67.5°	3.8
70°	1.9
72.5°	1.9
75°	1.9
77.5°	1.9
80°	1.9
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1252984

CATALOG NUMBER: P3AS24R259030D010 E3CB1MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)