

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253005

Luminaire Tested: P3AS24R259030D010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1253005
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS24R259030D010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R25 optic, 3000K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1533.0 lumens
Efficiency: N/A
Efficacy: 53.2 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1253005
CATALOG NUMBER: P3AS24R259030D010 E3DLD1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1253005
 CATALOG NUMBER: P3AS24R259030D010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91			91
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	89	87	85	83			83
3	100	92	87	82	98	91	86	82	88	84	80	86	82	79	83	80	78	76			76
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70			70
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64			64
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59			59
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55			55
8	75	65	58	54	74	64	58	53	63	57	53	62	57	53	61	56	53	51			51
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48			48
10	68	57	51	47	67	57	51	47	56	50	47	55	50	46	54	50	46	45			45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	364335
5°	355645
10°	329564
15°	293509
20°	252232
25°	214391
30°	176508
35°	137514
40°	98957
45°	62766
50°	37150
55°	25538
60°	23463
65°	21792
70°	19619
75°	17792
80°	16921
85°	14341

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 62766 cd/sqm



TEST NUMBER: P1253005
 CATALOG NUMBER: P3AS24R259030D010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.8	9.8
10°-20°	358.9	23.4
20°-30°	405.5	26.5
30°-40°	320.8	20.9
40°-50°	162.0	10.6
50°-60°	64.9	4.2
60°-70°	41.6	2.7
70°-80°	22.9	1.5
80°-90°	6.5	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	914.3	59.6
0°-40°	1235.1	80.6
0°-60°	1462.0	95.4
0°-90°	1533.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1533.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1662	
5°	1616	150
15°	1293	359
25°	886	406
35°	514	321
45°	202	162
55°	67	65
65°	42	42
75°	21	23
85°	6	6
90°	0	



TEST NUMBER: P1253005
CATALOG NUMBER: P3AS24R259030D010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1661.5
1°	1661.5
2°	1655.8
3°	1646.2
4°	1632.9
5°	1615.7
6°	1594.7
7°	1569.9
8°	1543.1
9°	1512.6
10°	1480.1
11°	1443.8
12°	1409.4
13°	1369.3
14°	1331.1
15°	1292.9
17.5°	1186.0
20°	1080.9
22.5°	981.6
25°	886.1
27.5°	792.6
30°	697.1
32.5°	607.3
35°	513.7
37.5°	427.8
40°	345.7
42.5°	269.3
45°	202.4
47.5°	150.9
50°	108.9
52.5°	82.1
55°	66.8
57.5°	61.1
60°	53.5
62.5°	47.7
65°	42.0
67.5°	36.3
70°	30.6
72.5°	26.7
75°	21.0
77.5°	17.2
80°	13.4
82.5°	9.5
85°	5.7
87.5°	1.9



TEST NUMBER: P1253005
CATALOG NUMBER: P3AS24R259030D010 E3DLD1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)