

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252121

Luminaire Tested: P3AS13R609030DE010 E3CB1MB

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1252121
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-40)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R609030DE010 E3CB1MB
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 90CRI , E3CB1MB TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1256.0 lumens
Efficiency: N/A
Efficacy: 86.0 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1252121

CATALOG NUMBER: P3AS13R609030DE010 E3CB1MB

Luminous Intensity Polar Plot



TEST NUMBER: P1252121

CATALOG NUMBER: P3AS13R609030DE010 E3CB1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94		
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87		
3	103	96	91	88	101	95	90	87	92	89	85	90	87	84	88	85	83	81		
4	98	90	85	81	96	89	84	80	87	83	79	85	81	78	83	80	77	76		
5	93	84	79	74	91	84	78	74	82	77	73	80	76	73	79	75	72	71		
6	88	79	73	69	87	79	73	69	77	72	68	76	71	68	74	70	68	66		
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62		
8	80	70	64	60	78	70	64	60	69	64	60	68	63	60	67	62	59	58		
9	76	66	61	57	75	66	60	56	65	60	56	64	59	56	63	59	56	55		
10	72	63	57	53	71	62	57	53	62	56	53	61	56	53	60	56	53	51		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	299932
5°	288025
10°	296543
15°	300365
20°	265230
25°	223513
30°	181268
35°	118052
40°	54216
45°	20777
50°	6959
55°	1873
60°	1710
65°	1505
70°	1218
75°	1610
80°	1263
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 20777 cd/sqm

TEST NUMBER: P1252121

CATALOG NUMBER: P3AS13R609030DE010 E3CB1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.9	10.0
10°-20°	362.3	28.8
20°-30°	422.6	33.6
30°-40°	272.7	21.7
40°-50°	61.1	4.9
50°-60°	6.1	0.5
60°-70°	2.9	0.2
70°-80°	1.6	0.1
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	910.9	72.5
0°-40°	1183.5	94.2
0°-60°	1250.8	99.6
0°-90°	1256.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1256.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1368	
5°	1308	126
15°	1323	362
25°	924	423
35°	441	273
45°	67	61
55°	5	6
65°	3	3
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1252121

CATALOG NUMBER: P3AS13R609030DE010 E3CB1MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	1367.8
2.5°	1345.4
5°	1308.5
7.5°	1306.6
10°	1331.8
12.5°	1348.3
15°	1323.1
17.5°	1247.3
20°	1136.6
22.5°	1021.0
25°	923.8
27.5°	828.6
30°	715.9
32.5°	583.8
35°	441.0
37.5°	301.1
40°	189.4
42.5°	113.7
45°	67.0
47.5°	38.9
50°	20.4
52.5°	6.8
55°	4.9
57.5°	3.9
60°	3.9
62.5°	2.9
65°	2.9
67.5°	2.9
70°	1.9
72.5°	1.9
75°	1.9
77.5°	1.0
80°	1.0
82.5°	1.0
85°	1.0
87.5°	0.0
90°	0.0

(END OF REPORT)