

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253006

Luminaire Tested: P3AS24R259030D010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1253006
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS24R259030D010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R25 optic, 3000K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 600.0 lumens
Efficiency: N/A
Efficacy: 20.8 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1253006
CATALOG NUMBER: P3AS24R259030D010 E3DLP1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1253006

CATALOG NUMBER: P3AS24R259030D010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93	93	93	93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86	86	86	86
3	102	95	90	86	100	94	89	86	91	87	84	89	86	83	87	84	82	80	80	80	80
4	97	89	84	79	95	88	83	79	86	81	78	84	80	77	82	79	76	75	75	75	75
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70	70	70	70
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	66	66	66	66
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62	62	62	62
8	80	70	65	60	79	70	64	60	69	64	60	68	63	60	67	63	60	58	58	58	58
9	76	67	61	57	75	66	61	57	65	60	57	65	60	57	64	59	56	55	55	55	55
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52	52	52	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	217833
5°	208980
10°	183074
15°	147152
20°	113060
25°	85553
30°	61807
35°	41064
40°	24904
45°	14513
50°	9245
55°	7493
60°	6578
65°	5811
70°	4809
75°	4745
80°	3536
85°	4780

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 14513 cd/sqm



TEST NUMBER: P1253006
 CATALOG NUMBER: P3AS24R259030D010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.4	14.4
10°-20°	179.2	29.9
20°-30°	162.1	27.0
30°-40°	97.4	16.2
40°-50°	38.7	6.4
50°-60°	17.8	3.0
60°-70°	10.9	1.8
70°-80°	5.8	1.0
80°-90°	1.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	427.8	71.3
0°-40°	525.1	87.5
0°-60°	581.6	96.9
0°-90°	600.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	600.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	993	
5°	949	86
15°	648	179
25°	354	162
35°	153	97
45°	47	39
55°	20	18
65°	11	11
75°	6	6
85°	2	2
90°	0	



TEST NUMBER: P1253006
CATALOG NUMBER: P3AS24R259030D010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	993.4
1°	993.4
2°	988.7
3°	978.4
4°	965.3
5°	949.4
6°	928.9
7°	905.5
8°	878.3
9°	851.2
10°	822.2
11°	788.5
12°	753.9
13°	719.3
14°	684.7
15°	648.2
17.5°	562.2
20°	484.5
22.5°	414.4
25°	353.6
27.5°	296.5
30°	244.1
32.5°	196.4
35°	153.4
37.5°	116.9
40°	87.0
42.5°	63.6
45°	46.8
47.5°	35.5
50°	27.1
52.5°	22.4
55°	19.6
57.5°	16.8
60°	15.0
62.5°	12.2
65°	11.2
67.5°	9.4
70°	7.5
72.5°	6.5
75°	5.6
77.5°	4.7
80°	2.8
82.5°	1.9
85°	1.9
87.5°	0.9



TEST NUMBER: P1253006
CATALOG NUMBER: P3AS24R259030D010 E3DLP1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)