

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253016

Luminaire Tested: P3AS24R309030D010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1253016
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-16)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS24R309030D010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R30 optic, 3000K CCT AND, 90CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2430.9 lumens
Efficiency: N/A
Efficacy: 84.4 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.47
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1253016

CATALOG NUMBER: P3AS24R309030D010 E3CB1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1253016

CATALOG NUMBER: P3AS24R309030D010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	96	95
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	93	92
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	94	92	91	90	89
4	105	100	96	93	103	99	95	92	97	94	91	95	92	90	93	91	89	88	87	86
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	87	85	84	83
6	99	93	89	86	98	92	88	86	91	88	85	90	87	85	89	86	84	83	82	81
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	80	79
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	78	77
9	91	85	81	78	90	84	81	78	84	80	78	83	80	78	82	79	77	76	75	74
10	89	83	79	76	88	82	78	76	82	78	76	81	78	76	80	77	75	74	73	72

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1979644
5°	1942236
10°	1719385
15°	1089337
20°	413503
25°	122426
30°	48337
35°	14830
40°	6555
45°	2357
50°	1944
55°	1453
60°	1667
65°	1972
70°	1218
75°	1610
80°	2399
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 80°
Luminance: 2399 cd/sqm

TEST NUMBER: P1253016

CATALOG NUMBER: P3AS24R309030D010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	811.1	33.4
10°-20°	1264.1	52.0
20°-30°	293.5	12.1
30°-40°	45.5	1.9
40°-50°	7.8	0.3
50°-60°	3.6	0.1
60°-70°	3.0	0.1
70°-80°	2.0	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2368.8	97.4
0°-40°	2414.3	99.3
0°-60°	2425.6	99.8
0°-90°	2430.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2430.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9028	
5°	8824	811
15°	4798	1264
25°	506	294
35°	55	45
45°	8	8
55°	4	4
65°	4	3
75°	2	2
85°	0	0
90°	0	

TEST NUMBER: P1253016

CATALOG NUMBER: P3AS24R309030D010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	9027.9
1°	9022.2
2°	8997.4
3°	8955.4
4°	8901.9
5°	8823.6
6°	8726.2
7°	8581.1
8°	8382.5
9°	8090.4
10°	7721.9
11°	7246.4
12°	6709.9
13°	6114.1
14°	5459.2
15°	4798.5
17.5°	3139.2
20°	1772.0
22.5°	905.1
25°	506.0
27.5°	311.2
30°	190.9
32.5°	103.1
35°	55.4
37.5°	36.3
40°	22.9
42.5°	13.4
45°	7.6
47.5°	5.7
50°	5.7
52.5°	3.8
55°	3.8
57.5°	3.8
60°	3.8
62.5°	3.8
65°	3.8
67.5°	1.9
70°	1.9
72.5°	1.9
75°	1.9
77.5°	1.9
80°	1.9
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1253016

CATALOG NUMBER: P3AS24R309030D010 E3CB1MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)