

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252138

Luminaire Tested: P3AS13R609030DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1252138
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-38)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R609030DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 393.0 lumens
Efficiency: N/A
Efficacy: 26.9 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1252138

CATALOG NUMBER: P3AS13R609030DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1252138

CATALOG NUMBER: P3AS13R609030DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	65	74	68	64		72	67	63		71
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	68	57	51	46	67	57	50	46	56	50	46		55	49	46		54
10	65	54	47	43	64	53	47	43	52	47	43		52	46	42		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	69753
5°	68985
10°	66599
15°	62906
20°	57988
25°	52503
30°	46615
35°	39833
40°	31688
45°	22328
50°	13339
55°	6729
60°	6491
65°	5915
70°	5514
75°	5253
80°	4799
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 22328 cd/sqm

TEST NUMBER: P1252138

CATALOG NUMBER: P3AS13R609030DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	29.4	7.5
10°-20°	77.5	19.7
20°-30°	99.4	25.3
30°-40°	92.2	23.5
40°-50°	56.1	14.3
50°-60°	18.7	4.8
60°-70°	11.4	2.9
70°-80°	6.4	1.6
80°-90°	1.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	206.3	52.5
0°-40°	298.5	76.0
0°-60°	373.4	95.0
0°-90°	393.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	393.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	318	
5°	313	29
15°	277	77
25°	217	99
35°	149	92
45°	72	56
55°	18	19
65°	11	11
75°	6	6
85°	1	2
90°	0	

TEST NUMBER: P1252138

CATALOG NUMBER: P3AS13R609030DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	318.1
2.5°	316.7
5°	313.4
7.5°	307.2
10°	299.1
12.5°	289.1
15°	277.1
17.5°	263.3
20°	248.5
22.5°	232.8
25°	217.0
27.5°	200.8
30°	184.1
32.5°	167.4
35°	148.8
37.5°	129.3
40°	110.7
42.5°	91.1
45°	72.0
47.5°	55.8
50°	39.1
52.5°	23.4
55°	17.6
57.5°	16.2
60°	14.8
62.5°	12.9
65°	11.4
67.5°	10.0
70°	8.6
72.5°	7.2
75°	6.2
77.5°	4.8
80°	3.8
82.5°	2.4
85°	1.4
87.5°	1.0
90°	0.0

(END OF REPORT)