

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252143

Luminaire Tested: P3AS13R609030DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1252143
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-38)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R609030DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 800.9 lumens
Efficiency: N/A
Efficacy: 54.9 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1252143

CATALOG NUMBER: P3AS13R609030DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1252143

CATALOG NUMBER: P3AS13R609030DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	65	74	68	64		72	67	63		71
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	68	57	51	46	67	57	50	46	56	50	46		55	49	46		54
10	65	54	47	43	64	53	47	43	52	47	43		52	46	42		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	142182
5°	140590
10°	135713
15°	128219
20°	118194
25°	107014
30°	95027
35°	81191
40°	64550
45°	45524
50°	27189
55°	13763
60°	13201
65°	12089
70°	11220
75°	10675
80°	9850
85°	7296

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 45524 cd/sqm

TEST NUMBER: P1252143

CATALOG NUMBER: P3AS13R609030DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.0	7.5
10°-20°	157.8	19.7
20°-30°	202.7	25.3
30°-40°	187.9	23.5
40°-50°	114.4	14.3
50°-60°	38.1	4.8
60°-70°	23.2	2.9
70°-80°	13.1	1.6
80°-90°	3.7	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	420.6	52.5
0°-40°	608.5	76.0
0°-60°	761.0	95.0
0°-90°	800.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	800.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	648	
5°	639	60
15°	565	158
25°	442	203
35°	303	188
45°	147	114
55°	36	38
65°	23	23
75°	13	13
85°	3	4
90°	0	

TEST NUMBER: P1252143

CATALOG NUMBER: P3AS13R609030DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	648.4
2.5°	645.5
5°	638.7
7.5°	626.1
10°	609.5
12.5°	589.1
15°	564.8
17.5°	536.6
20°	506.5
22.5°	474.4
25°	442.3
27.5°	409.3
30°	375.3
32.5°	341.2
35°	303.3
37.5°	263.5
40°	225.5
42.5°	185.7
45°	146.8
47.5°	113.7
50°	79.7
52.5°	47.6
55°	36.0
57.5°	33.1
60°	30.1
62.5°	26.2
65°	23.3
67.5°	20.4
70°	17.5
72.5°	14.6
75°	12.6
77.5°	9.7
80°	7.8
82.5°	4.9
85°	2.9
87.5°	1.9
90°	0.0

(END OF REPORT)