

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252149

Luminaire Tested: P3AS13R609030DE010 E3DLP1WMH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1252149  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R609030DE010 E3DLP1WMH  
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 90CRI , E3DLP1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 707.0 lumens  
Efficiency: N/A  
Efficacy: 48.4 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 14.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1252149  
CATALOG NUMBER: P3AS13R609030DE010 E3DLP1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P1252149  
 CATALOG NUMBER: P3AS13R609030DE010 E3DLP1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92				92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85				85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78				78
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72				72
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66				66
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	66	63	62				62
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	58				58
8	77	67	60	56	75	66	60	56	65	60	56	64	59	55	63	58	55	54				54
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50				50
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47				47

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	179174
5°	175148
10°	163992
15°	147129
20°	126501
25°	104619
30°	82671
35°	61382
40°	42279
45°	26514
50°	14567
55°	8525
60°	7675
65°	6538
70°	5578
75°	5761
80°	4925
85°	4780

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 26514 cd/sqm



TEST NUMBER: P1252149  
 CATALOG NUMBER: P3AS13R609030DE010 E3DLP1WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	74.1	10.5
10°-20°	180.0	25.5
20°-30°	197.4	27.9
30°-40°	143.8	20.3
40°-50°	67.9	9.6
50°-60°	22.2	3.1
60°-70°	12.6	1.8
70°-80°	6.8	1.0
80°-90°	2.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	451.5	63.9
0°-40°	595.3	84.2
0°-60°	685.5	97.0
0°-90°	707.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	707.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	817	
5°	796	74
15°	648	180
25°	432	197
35°	229	144
45°	86	68
55°	22	22
65°	13	13
75°	7	7
85°	2	2
90°	0	



TEST NUMBER: P1252149  
CATALOG NUMBER: P3AS13R609030DE010 E3DLP1WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	817.1
2.5°	812.2
5°	795.7
7.5°	770.5
10°	736.5
12.5°	695.7
15°	648.1
17.5°	596.6
20°	542.1
22.5°	486.8
25°	432.4
27.5°	377.9
30°	326.5
32.5°	276.9
35°	229.3
37.5°	186.5
40°	147.7
42.5°	113.7
45°	85.5
47.5°	62.2
50°	42.7
52.5°	28.2
55°	22.3
57.5°	19.4
60°	17.5
62.5°	14.6
65°	12.6
67.5°	10.7
70°	8.7
72.5°	7.8
75°	6.8
77.5°	4.9
80°	3.9
82.5°	2.9
85°	1.9
87.5°	1.0
90°	0.0

(END OF REPORT)