

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252231

Luminaire Tested: P3AS17R129030DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1252231
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R129030DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R12 optic, 3000K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 660.0 lumens
Efficiency: N/A
Efficacy: 28.8 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 22.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1252231

CATALOG NUMBER: P3AS17R129030DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1252231

CATALOG NUMBER: P3AS17R129030DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	106	111	108	106	104	104	102	101		100	99	98		97
2	108	103	98	95	105	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	93	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	87	79	73	69	77	72	69		76	71	68		74
7	84	75	69	65	83	74	69	65	73	68	64		72	67	64		71
8	80	71	65	61	79	71	65	61	69	64	61		68	64	61		67
9	77	68	62	58	76	67	62	58	66	61	58		65	61	57		64
10	74	64	59	55	73	64	59	55	63	58	55		62	58	55		62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	284604
5°	263041
10°	210016
15°	158639
20°	120807
25°	92062
30°	65934
35°	43045
40°	26392
45°	15940
50°	10609
55°	8181
60°	7061
65°	6123
70°	5514
75°	5422
80°	4041
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15940 cd/sqm

TEST NUMBER: P1252231

CATALOG NUMBER: P3AS17R129030DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.9	16.0
10°-20°	195.3	29.6
20°-30°	173.9	26.3
30°-40°	102.9	15.6
40°-50°	42.2	6.4
50°-60°	19.8	3.0
60°-70°	12.1	1.8
70°-80°	6.4	1.0
80°-90°	1.6	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	475.1	72.0
0°-40°	578.0	87.6
0°-60°	640.0	97.0
0°-90°	660.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	660.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1298	
5°	1195	106
15°	699	195
25°	380	174
35°	161	103
45°	51	42
55°	21	20
65°	12	12
75°	6	6
85°	1	2
90°	0	

TEST NUMBER: P1252231

CATALOG NUMBER: P3AS17R129030DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1297.9
1°	1294.7
2°	1285.0
3°	1265.8
4°	1233.6
5°	1195.0
6°	1153.2
7°	1103.9
8°	1052.5
9°	1000.0
10°	943.2
12.5°	813.5
15°	698.8
17.5°	600.2
20°	517.7
22.5°	444.8
25°	380.5
27.5°	318.3
30°	260.4
32.5°	207.9
35°	160.8
37.5°	123.3
40°	92.2
42.5°	68.6
45°	51.4
47.5°	39.7
50°	31.1
52.5°	25.7
55°	21.4
57.5°	18.2
60°	16.1
62.5°	13.9
65°	11.8
67.5°	10.7
70°	8.6
72.5°	7.5
75°	6.4
77.5°	4.3
80°	3.2
82.5°	2.1
85°	1.1
87.5°	1.1
90°	0.0

(END OF REPORT)