

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253105

Luminaire Tested: P3AS24R459030D010 E3CB1MMS

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1253105  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-28)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS24R459030D010 E3CB1MMS  
Description: 3in Adjustable LED luminaire with, R45 optic, 3000K CCT AND, 90CRI , E3CB1MMS TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2560.9 lumens  
Efficiency: N/A  
Efficacy: 88.9 lumens/watt  
Spacing Criteria (0/90/45): 0.72 / 0.72 / 0.66  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1253105

CATALOG NUMBER: P3AS24R459030D010 E3CB1MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P1253105

CATALOG NUMBER: P3AS24R459030D010 E3CB1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 114 | 112 | 110 | 108 | 112 | 110 | 108 | 106 | 106 | 104 | 103 |  | 102 | 101 | 100 |  | 99  |
| 2   | 110 | 106 | 102 | 100 | 108 | 104 | 101 | 98  | 101 | 98  | 96  |  | 98  | 96  | 94  |  | 95  |
| 3   | 106 | 100 | 96  | 93  | 104 | 99  | 95  | 92  | 96  | 93  | 91  |  | 94  | 91  | 89  |  | 92  |
| 4   | 102 | 95  | 91  | 87  | 100 | 94  | 90  | 87  | 92  | 89  | 86  |  | 90  | 87  | 85  |  | 88  |
| 5   | 98  | 91  | 86  | 82  | 96  | 90  | 85  | 82  | 88  | 84  | 81  |  | 87  | 83  | 81  |  | 85  |
| 6   | 94  | 87  | 82  | 78  | 93  | 86  | 81  | 78  | 85  | 80  | 77  |  | 83  | 80  | 77  |  | 82  |
| 7   | 90  | 83  | 78  | 74  | 89  | 82  | 78  | 74  | 81  | 77  | 74  |  | 80  | 76  | 74  |  | 79  |
| 8   | 87  | 79  | 74  | 71  | 86  | 79  | 74  | 71  | 78  | 74  | 71  |  | 77  | 73  | 70  |  | 76  |
| 9   | 84  | 76  | 71  | 68  | 83  | 76  | 71  | 68  | 75  | 71  | 68  |  | 74  | 70  | 67  |  | 73  |
| 10  | 81  | 73  | 68  | 65  | 80  | 73  | 68  | 65  | 72  | 68  | 65  |  | 71  | 67  | 65  |  | 71  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 1110328 |
| 5°  | 1116264 |
| 10° | 1081966 |
| 15° | 906679  |
| 20° | 693084  |
| 25° | 421936  |
| 30° | 175546  |
| 35° | 56242   |
| 40° | 17490   |
| 45° | 3566    |
| 50° | 2593    |
| 55° | 2906    |
| 60° | 2500    |
| 65° | 2958    |
| 70° | 2436    |
| 75° | 3219    |
| 80° | 2399    |
| 85° | 0       |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
Vertical Angle: 45°  
Luminance: 3566 cd/sqm

TEST NUMBER: P1253105

CATALOG NUMBER: P3AS24R459030D010 E3CB1MMS

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 478.3  | 18.7      |
| 10°-20°   | 1097.7 | 42.9      |
| 20°-30°   | 790.4  | 30.9      |
| 30°-40°   | 164.4  | 6.4       |
| 40°-50°   | 15.0   | 0.6       |
| 50°-60°   | 6.2    | 0.2       |
| 60°-70°   | 4.9    | 0.2       |
| 70°-80°   | 3.3    | 0.1       |
| 80°-90°   | 0.8    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 2366.3 | 92.4      |
| 0°-40°    | 2530.7 | 98.8      |
| 0°-60°    | 2551.9 | 99.6      |
| 0°-90°    | 2560.9 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 2560.9 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 5064 |      |
| 5°  | 5071 | 478  |
| 15° | 3994 | 1098 |
| 25° | 1744 | 790  |
| 35° | 210  | 164  |
| 45° | 12   | 15   |
| 55° | 8    | 6    |
| 65° | 6    | 5    |
| 75° | 4    | 3    |
| 85° | 0    | 1    |
| 90° | 0    |      |

TEST NUMBER: P1253105

CATALOG NUMBER: P3AS24R459030D010 E3CB1MMS

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 5063.5 |
| 2.5°  | 5065.4 |
| 5°    | 5071.2 |
| 7.5°  | 5034.9 |
| 10°   | 4859.2 |
| 12.5° | 4492.4 |
| 15°   | 3993.9 |
| 17.5° | 3483.9 |
| 20°   | 2970.1 |
| 22.5° | 2379.9 |
| 25°   | 1743.9 |
| 27.5° | 1149.8 |
| 30°   | 693.3  |
| 32.5° | 387.7  |
| 35°   | 210.1  |
| 37.5° | 118.4  |
| 40°   | 61.1   |
| 42.5° | 26.7   |
| 45°   | 11.5   |
| 47.5° | 7.6    |
| 50°   | 7.6    |
| 52.5° | 7.6    |
| 55°   | 7.6    |
| 57.5° | 5.7    |
| 60°   | 5.7    |
| 62.5° | 5.7    |
| 65°   | 5.7    |
| 67.5° | 3.8    |
| 70°   | 3.8    |
| 72.5° | 3.8    |
| 75°   | 3.8    |
| 77.5° | 1.9    |
| 80°   | 1.9    |
| 82.5° | 1.9    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |

(END OF REPORT)