

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252271

Luminaire Tested: P3AS17R209030DE010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1252271
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R209030DE010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R20 optic, 3000K CCT AND, 90CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1626.1 lumens
Efficiency: N/A
Efficacy: 76.7 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1252271

CATALOG NUMBER: P3AS17R209030DE010 E3CD1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1252271

CATALOG NUMBER: P3AS17R209030DE010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	116	114	112	110	113	112	110	109	108	106	105		104	103	102		101
2	112	109	107	104	110	108	105	103	104	103	101		102	100	99		99
3	109	105	102	100	108	104	101	99	102	99	97		99	98	96		97
4	107	102	99	96	105	101	98	96	99	97	95		97	95	93		96
5	104	99	96	93	103	98	95	93	97	94	92		95	93	91		94
6	102	97	93	91	101	96	93	90	95	92	90		94	91	89		93
7	100	94	91	88	99	94	91	88	93	90	88		92	89	87		91
8	98	92	89	86	97	92	89	86	91	88	86		90	88	86		89
9	96	90	87	85	95	90	87	85	89	86	84		89	86	84		88
10	94	89	85	83	93	88	85	83	88	85	83		87	84	83		86

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2525368
5°	2191938
10°	1354373
15°	470423
20°	144469
25°	51076
30°	18889
35°	7576
40°	4065
45°	1582
50°	887
55°	994
60°	1140
65°	675
70°	833
75°	1101
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1582 cd/sqm

TEST NUMBER: P1252271

CATALOG NUMBER: P3AS17R209030DE010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	826.4	50.8
10°-20°	655.7	40.3
20°-30°	113.5	7.0
30°-40°	20.6	1.3
40°-50°	4.7	0.3
50°-60°	2.3	0.1
60°-70°	1.4	0.1
70°-80°	1.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1595.7	98.1
0°-40°	1616.3	99.4
0°-60°	1623.4	99.8
0°-90°	1626.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1626.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11517	
5°	9958	826
15°	2072	656
25°	211	114
35°	28	21
45°	5	5
55°	3	2
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1252271

CATALOG NUMBER: P3AS17R209030DE010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	11516.6
1°	11461.2
2°	11242.4
3°	10891.1
4°	10479.2
5°	9958.0
6°	9360.8
7°	8665.7
8°	7874.2
9°	6984.9
10°	6082.6
12.5°	3836.7
15°	2072.2
17.5°	1106.9
20°	619.1
22.5°	353.9
25°	211.1
27.5°	128.7
30°	74.6
32.5°	43.8
35°	28.3
37.5°	19.3
40°	14.2
42.5°	9.0
45°	5.1
47.5°	2.6
50°	2.6
52.5°	2.6
55°	2.6
57.5°	2.6
60°	2.6
62.5°	1.3
65°	1.3
67.5°	1.3
70°	1.3
72.5°	1.3
75°	1.3
77.5°	1.3
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)