

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253130

Luminaire Tested: P3AS24R509030D010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1253130
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-32)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS24R509030D010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R50 optic, 3000K CCT AND, 90CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2613.9 lumens
Efficiency: N/A
Efficacy: 90.8 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1253130
CATALOG NUMBER: P3AS24R509030D010 E3CB1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1253130
 CATALOG NUMBER: P3AS24R509030D010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	97	95			
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	90			
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85			
4	100	94	89	85	99	92	88	85	90	87	84	88	85	83	87	84	82	80			
5	96	89	84	80	94	88	83	79	86	82	79	84	81	78	83	80	77	76			
6	92	84	79	75	91	83	79	75	82	78	74	81	77	74	79	76	73	72			
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	69			
8	85	76	71	67	83	76	71	67	75	70	67	74	70	67	73	69	66	65			
9	81	73	68	64	80	72	67	64	71	67	64	71	66	63	70	66	63	62			
10	78	69	64	61	77	69	64	61	68	64	61	68	63	61	67	63	60	59			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	910388
5°	894098
10°	858479
15°	787224
20°	694157
25°	532071
30°	289285
35°	93077
40°	21870
45°	2977
50°	2593
55°	2906
60°	2500
65°	2958
70°	2436
75°	3219
80°	2399
85°	4780

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 85°
 Luminance: 4780 cd/sqm



TEST NUMBER: P1253130
 CATALOG NUMBER: P3AS24R509030D010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	381.2	14.6
10°-20°	963.9	36.9
20°-30°	965.4	36.9
30°-40°	271.4	10.4
40°-50°	16.4	0.6
50°-60°	6.2	0.2
60°-70°	4.9	0.2
70°-80°	3.3	0.1
80°-90°	1.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2310.5	88.4
0°-40°	2581.9	98.8
0°-60°	2604.4	99.6
0°-90°	2613.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2613.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4152	
5°	4062	381
15°	3468	964
25°	2199	965
35°	348	271
45°	10	16
55°	8	6
65°	6	5
75°	4	3
85°	2	1
90°	0	



TEST NUMBER: P1253130
CATALOG NUMBER: P3AS24R509030D010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	4151.7
2.5°	4130.6
5°	4061.9
7.5°	3968.2
10°	3855.5
12.5°	3685.5
15°	3467.7
17.5°	3217.4
20°	2974.7
22.5°	2672.9
25°	2199.1
27.5°	1637.4
30°	1142.5
32.5°	689.7
35°	347.7
37.5°	164.3
40°	76.4
42.5°	28.7
45°	9.6
47.5°	7.6
50°	7.6
52.5°	7.6
55°	7.6
57.5°	5.7
60°	5.7
62.5°	5.7
65°	5.7
67.5°	3.8
70°	3.8
72.5°	3.8
75°	3.8
77.5°	1.9
80°	1.9
82.5°	1.9
85°	1.9
87.5°	0.0
90°	0.0

(END OF REPORT)