

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252288

Luminaire Tested: P3AS17R209030DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1252288
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R209030DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R20 optic, 3000K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1014.0 lumens
Efficiency: N/A
Efficacy: 47.8 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1252288

CATALOG NUMBER: P3AS17R209030DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1252288

CATALOG NUMBER: P3AS17R209030DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		90
3	100	93	87	82	98	91	86	82	88	84	80		86	82	79		84
4	94	86	79	75	92	85	79	74	82	77	73		80	76	72		78
5	89	80	73	68	87	79	73	68	77	71	67		75	70	67		73
6	84	74	68	63	82	73	67	63	72	66	62		70	65	62		69
7	80	69	63	58	78	69	62	58	67	62	58		66	61	57		65
8	75	65	59	54	74	64	58	54	63	58	54		62	57	53		61
9	72	61	55	50	70	61	55	50	60	54	50		59	54	50		58
10	68	58	51	47	67	57	51	47	56	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	250813
5°	244111
10°	224578
15°	197663
20°	169531
25°	142411
30°	115132
35°	87589
40°	62317
45°	41152
50°	25483
55°	16745
60°	15262
65°	14009
70°	13207
75°	12031
80°	11365
85°	9812

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 41152 cd/sqm

TEST NUMBER: P1252288

CATALOG NUMBER: P3AS17R209030DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.6	10.1
10°-20°	242.4	23.9
20°-30°	269.1	26.5
30°-40°	205.3	20.2
40°-50°	105.1	10.4
50°-60°	43.2	4.3
60°-70°	26.9	2.7
70°-80°	15.1	1.5
80°-90°	4.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	614.1	60.6
0°-40°	819.3	80.8
0°-60°	967.6	95.4
0°-90°	1014.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1014.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1144	
5°	1109	103
15°	871	242
25°	589	269
35°	327	205
45°	133	105
55°	44	43
65°	27	27
75°	14	15
85°	4	4
90°	0	

TEST NUMBER: P1252288

CATALOG NUMBER: P3AS17R209030DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1143.8
1°	1145.1
2°	1139.9
3°	1133.5
4°	1123.2
5°	1109.0
6°	1092.3
7°	1074.2
8°	1054.9
9°	1031.7
10°	1008.6
12.5°	941.6
15°	870.7
17.5°	798.6
20°	726.5
22.5°	654.3
25°	588.6
27.5°	523.0
30°	454.7
32.5°	390.3
35°	327.2
37.5°	271.8
40°	217.7
42.5°	171.3
45°	132.7
47.5°	100.5
50°	74.7
52.5°	55.4
55°	43.8
57.5°	39.9
60°	34.8
62.5°	30.9
65°	27.0
67.5°	23.2
70°	20.6
72.5°	16.7
75°	14.2
77.5°	11.6
80°	9.0
82.5°	6.4
85°	3.9
87.5°	1.3
90°	0.0

(END OF REPORT)