

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252367

Luminaire Tested: P3AS17R359030DE010 E3DL1MW

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1252367  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R359030DE010 E3DL1MW  
Description: 3in Adjustable LED luminaire with, R35 optic, 3000K CCT AND, 90CRI , E3DL1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1353.0 lumens  
Efficiency: N/A  
Efficacy: 63.8 lumens/watt  
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 21.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1252367  
CATALOG NUMBER: P3AS17R359030DE010 E3DL1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1252367

CATALOG NUMBER: P3AS17R359030DE010 E3DL1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	95	95	95	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	90	90	90	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85	85	85	85
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80	80	80	80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76	76	76	76
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	73	73	73	73
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	70	70	70	70
8	85	77	72	69	84	77	72	68	76	71	68	75	71	68	74	70	68	66	66	66	66
9	82	74	69	66	81	74	69	65	73	68	65	72	68	65	71	68	65	64	64	64	64
10	79	71	66	63	78	71	66	63	70	66	63	69	65	62	69	65	62	61	61	61	61

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	682401
5°	655820
10°	571421
15°	437664
20°	292812
25°	177180
30°	101661
35°	56858
40°	30199
45°	15568
50°	7471
55°	5887
60°	5657
65°	4670
70°	4937
75°	4321
80°	4925
85°	3271

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 15568 cd/sqm

TEST NUMBER: P1252367  
 CATALOG NUMBER: P3AS17R359030DE010 E3DL1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	271.1	20.0
10°-20°	525.3	38.8
20°-30°	343.9	25.4
30°-40°	139.5	10.3
40°-50°	41.9	3.1
50°-60°	14.2	1.1
60°-70°	9.5	0.7
70°-80°	5.6	0.4
80°-90°	1.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1140.3	84.3
0°-40°	1279.8	94.6
0°-60°	1335.9	98.7
0°-90°	1353.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1353.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3112	
5°	2979	271
15°	1928	525
25°	732	344
35°	212	140
45°	50	42
55°	15	14
65°	9	10
75°	5	6
85°	1	2
90°	0	



TEST NUMBER: P1252367  
CATALOG NUMBER: P3AS17R359030DE010 E3DL1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3112.0
1°	3106.8
2°	3092.7
3°	3064.3
4°	3030.9
5°	2979.4
6°	2915.1
7°	2843.0
8°	2761.9
9°	2669.2
10°	2566.3
11°	2451.7
12°	2332.0
13°	2198.2
14°	2070.8
15°	1927.9
17.5°	1581.7
20°	1254.8
22.5°	965.3
25°	732.3
27.5°	545.7
30°	401.5
32.5°	294.7
35°	212.4
37.5°	150.6
40°	105.5
42.5°	73.4
45°	50.2
47.5°	33.5
50°	21.9
52.5°	16.7
55°	15.4
57.5°	14.2
60°	12.9
62.5°	11.6
65°	9.0
67.5°	7.7
70°	7.7
72.5°	6.4
75°	5.1
77.5°	3.9
80°	3.9
82.5°	2.6
85°	1.3
87.5°	1.3



TEST NUMBER: P1252367  
CATALOG NUMBER: P3AS17R359030DE010 E3DL1MW

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)