

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253210

Luminaire Tested: P3AS24R609030D010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1253210
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS24R609030D010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 681.0 lumens
Efficiency: N/A
Efficacy: 23.6 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1253210

CATALOG NUMBER: P3AS24R609030D010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1253210

CATALOG NUMBER: P3AS24R609030D010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		92
2	107	101	97	93	104	100	96	92	96	93	90		93	91	88		85
3	101	94	88	84	99	92	87	83	90	86	82		87	84	81		78
4	95	87	81	77	93	86	80	76	84	79	75		82	78	74		72
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		66
6	85	76	69	65	84	75	69	65	73	68	64		72	67	64		62
7	81	71	65	60	79	70	64	60	69	64	60		68	63	59		58
8	77	67	60	56	75	66	60	56	65	60	56		64	59	55		54
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		50
10	69	59	53	49	68	59	53	49	58	53	49		57	52	49		47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	172596
5°	168721
10°	157957
15°	141703
20°	121857
25°	100772
30°	79607
35°	59133
40°	40733
45°	25553
50°	14055
55°	8220
60°	7368
65°	6330
70°	5386
75°	5592
80°	4672
85°	4780

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 25553 cd/sqm

TEST NUMBER: P1253210

CATALOG NUMBER: P3AS24R609030D010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	71.4	10.5
10°-20°	173.4	25.5
20°-30°	190.2	27.9
30°-40°	138.5	20.3
40°-50°	65.5	9.6
50°-60°	21.4	3.1
60°-70°	12.1	1.8
70°-80°	6.6	1.0
80°-90°	2.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	434.9	63.9
0°-40°	573.4	84.2
0°-60°	660.3	97.0
0°-90°	681.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	681.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	787	
5°	766	71
15°	624	173
25°	416	190
35°	221	139
45°	82	65
55°	22	21
65°	12	12
75°	7	7
85°	2	2
90°	0	

TEST NUMBER: P1253210

CATALOG NUMBER: P3AS24R609030D010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	787.1
2.5°	782.4
5°	766.5
7.5°	742.1
10°	709.4
12.5°	670.1
15°	624.2
17.5°	574.6
20°	522.2
22.5°	468.9
25°	416.5
27.5°	364.0
30°	314.4
32.5°	266.7
35°	220.9
37.5°	179.7
40°	142.3
42.5°	109.5
45°	82.4
47.5°	59.9
50°	41.2
52.5°	27.1
55°	21.5
57.5°	18.7
60°	16.8
62.5°	14.0
65°	12.2
67.5°	10.3
70°	8.4
72.5°	7.5
75°	6.6
77.5°	4.7
80°	3.7
82.5°	2.8
85°	1.9
87.5°	0.9
90°	0.0

(END OF REPORT)