

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252393

Luminaire Tested: P3AS17R409030DE010 E3D1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1252393
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-24)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R409030DE010 E3D1MW
Description: 3in Adjustable LED luminaire with, R40 optic, 3000K CCT AND, 90CRI , E3D1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1809.1 lumens
Efficiency: N/A
Efficacy: 85.3 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.59
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1252393
CATALOG NUMBER: P3AS17R409030DE010 E3D1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1252393

CATALOG NUMBER: P3AS17R409030DE010 E3D1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	112	110	109	112	110	109	107	106	105	104	103	102	101	99	98	98	96	96	96	96
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	96	95	94	92	92	92	92
3	107	102	98	95	105	100	97	94	98	95	93	96	93	91	94	92	90	89	89	89	89
4	103	97	93	90	102	96	92	89	94	91	88	92	90	87	91	88	86	85	85	85	85
5	100	93	89	86	98	92	88	85	91	87	85	89	86	84	88	85	83	82	82	82	82
6	96	90	85	82	95	89	85	82	88	84	81	86	83	81	85	82	80	79	79	79	79
7	93	86	82	79	92	86	81	78	85	81	78	83	80	78	82	79	77	76	76	76	76
8	90	83	79	76	89	83	78	75	82	78	75	81	77	75	80	77	75	74	74	74	74
9	87	80	76	73	87	80	76	73	79	75	72	78	75	72	77	74	72	71	71	71	71
10	85	77	73	70	84	77	73	70	76	73	70	76	72	70	75	72	70	69	69	69	69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	952489
5°	947895
10°	917017
15°	811310
20°	529339
25°	187511
30°	39778
35°	13090
40°	4780
45°	1582
50°	1330
55°	1491
60°	1140
65°	1349
70°	833
75°	1101
80°	1642
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 82.5°
 Luminance: 2184 cd/sqm



TEST NUMBER: P1252393
 CATALOG NUMBER: P3AS17R409030DE010 E3D1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	405.2	22.4
10°-20°	943.6	52.2
20°-30°	409.5	22.6
30°-40°	37.7	2.1
40°-50°	5.4	0.3
50°-60°	3.3	0.2
60°-70°	2.4	0.1
70°-80°	1.4	0.1
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1758.3	97.2
0°-40°	1796.1	99.3
0°-60°	1804.8	99.8
0°-90°	1809.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1809.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4344	
5°	4306	405
15°	3574	944
25°	775	409
35°	49	38
45°	5	5
55°	4	3
65°	3	2
75°	1	1
85°	0	1
90°	0	



TEST NUMBER: P1252393
CATALOG NUMBER: P3AS17R409030DE010 E3D1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	4343.7
2.5°	4338.5
5°	4306.3
7.5°	4238.1
10°	4118.4
12.5°	3916.3
15°	3573.8
17.5°	3006.1
20°	2268.4
22.5°	1472.8
25°	775.0
27.5°	333.4
30°	157.1
32.5°	85.0
35°	48.9
37.5°	29.6
40°	16.7
42.5°	9.0
45°	5.1
47.5°	3.9
50°	3.9
52.5°	3.9
55°	3.9
57.5°	3.9
60°	2.6
62.5°	2.6
65°	2.6
67.5°	2.6
70°	1.3
72.5°	1.3
75°	1.3
77.5°	1.3
80°	1.3
82.5°	1.3
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)