

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252396

Luminaire Tested: P3AS17R409030DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1252396
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R409030DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R40 optic, 3000K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 735.0 lumens
Efficiency: N/A
Efficacy: 34.7 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1252396

CATALOG NUMBER: P3AS17R409030DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1252396

CATALOG NUMBER: P3AS17R409030DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	112	109	107	105	105	104	102		102	100	99		98
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94
3	104	99	94	91	102	97	93	90	95	91	88		92	89	87		90
4	100	93	88	85	98	92	88	84	90	86	83		88	85	82		86
5	96	88	83	79	94	88	83	79	86	82	78		84	81	78		83
6	92	84	79	75	91	83	78	75	82	78	74		81	77	74		79
7	88	80	75	71	87	79	74	71	78	74	71		77	73	70		76
8	85	76	71	68	84	76	71	67	75	70	67		74	70	67		73
9	82	73	68	64	81	73	68	64	72	67	64		71	67	64		70
10	78	70	65	62	78	70	65	61	69	64	61		68	64	61		67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	325237
5°	315782
10°	286568
15°	236732
20°	170768
25°	105635
30°	57199
35°	29553
40°	16059
45°	8993
50°	4503
55°	3364
60°	3026
65°	2958
70°	2821
75°	2711
80°	2399
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8993 cd/sqm

TEST NUMBER: P1252396

CATALOG NUMBER: P3AS17R409030DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	132.2	18.0
10°-20°	284.0	38.6
20°-30°	202.7	27.6
30°-40°	74.6	10.1
40°-50°	23.5	3.2
50°-60°	8.2	1.1
60°-70°	5.6	0.8
70°-80°	3.3	0.5
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	618.9	84.2
0°-40°	693.4	94.3
0°-60°	725.1	98.7
0°-90°	735.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	735.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1483	
5°	1435	132
15°	1043	284
25°	437	203
35°	110	75
45°	29	23
55°	9	8
65°	6	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1252396

CATALOG NUMBER: P3AS17R409030DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1483.2
2.5°	1471.8
5°	1434.6
7.5°	1372.8
10°	1287.0
12.5°	1177.8
15°	1042.8
17.5°	891.4
20°	731.8
22.5°	574.7
25°	436.6
27.5°	320.5
30°	225.9
32.5°	158.3
35°	110.4
37.5°	78.2
40°	56.1
42.5°	40.4
45°	29.0
47.5°	19.6
50°	13.2
52.5°	9.5
55°	8.8
57.5°	8.2
60°	6.9
62.5°	6.3
65°	5.7
67.5°	5.0
70°	4.4
72.5°	3.8
75°	3.2
77.5°	2.5
80°	1.9
82.5°	1.3
85°	0.6
87.5°	0.6
90°	0.0

(END OF REPORT)