

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253226

Luminaire Tested: P3AS24R659030D010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1253226
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-16)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS24R659030D010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R65 optic, 3000K CCT AND, 90CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2278.0 lumens
Efficiency: N/A
Efficacy: 79.1 lumens/watt
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1253226

CATALOG NUMBER: P3AS24R659030D010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1253226

CATALOG NUMBER: P3AS24R659030D010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93
3	103	97	92	88	101	95	91	88	93	89	86		90	87	85		88
4	98	91	85	81	96	90	85	81	87	83	80		85	82	79		84
5	93	85	79	75	92	84	79	75	82	78	74		81	77	74		79
6	89	80	74	70	87	79	74	70	78	73	69		76	72	69		75
7	84	75	70	65	83	75	69	65	73	69	65		72	68	65		71
8	80	71	65	61	79	71	65	61	69	64	61		68	64	61		67
9	77	67	61	58	76	67	61	57	66	61	57		65	60	57		64
10	73	64	58	54	72	63	58	54	62	57	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	610412
5°	566783
10°	548108
15°	528198
20°	488339
25°	444921
30°	343774
35°	199270
40°	79062
45°	33678
50°	7983
55°	1070
60°	833
65°	467
70°	577
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 33678 cd/sqm

TEST NUMBER: P1253226

CATALOG NUMBER: P3AS24R659030D010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	242.8	10.7
10°-20°	648.3	28.5
20°-30°	820.5	36.0
30°-40°	467.3	20.5
40°-50°	92.8	4.1
50°-60°	4.8	0.2
60°-70°	1.3	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1711.7	75.1
0°-40°	2179.0	95.7
0°-60°	2276.6	99.9
0°-90°	2278.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2278.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2784	
5°	2575	243
15°	2327	648
25°	1839	821
35°	744	467
45°	109	93
55°	3	5
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1253226

CATALOG NUMBER: P3AS24R659030D010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2783.7
1°	2763.1
2°	2718.1
3°	2665.7
4°	2614.2
5°	2574.9
6°	2545.8
7°	2522.4
8°	2501.8
9°	2481.2
10°	2461.6
11°	2440.0
12°	2417.6
13°	2390.4
14°	2361.4
15°	2326.7
16°	2285.5
17°	2240.6
18°	2191.9
19°	2140.4
20°	2092.7
21°	2044.0
22°	2000.0
23°	1954.1
24°	1900.7
25°	1838.9
26°	1765.0
27°	1676.0
28°	1575.8
29°	1469.1
30°	1357.7
31°	1235.0
32°	1113.3
32.5°	1050.5
33°	989.7
34°	866.1
35°	744.4
36°	632.0
37°	520.6
37.5°	463.5
38°	417.6
39°	338.0
40°	276.2
42.5°	170.4
45°	108.6



TEST NUMBER: P1253226

CATALOG NUMBER: P3AS24R659030D010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	63.7
50°	23.4
52.5°	4.7
55°	2.8
57.5°	1.9
60°	1.9
62.5°	1.9
65°	0.9
67.5°	0.9
70°	0.9
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)