

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252402

Luminaire Tested: P3AS17R409030DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1252402
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R409030DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R40 optic, 3000K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 564.0 lumens
Efficiency: N/A
Efficacy: 26.6 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1252402

CATALOG NUMBER: P3AS17R409030DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1252402

CATALOG NUMBER: P3AS17R409030DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91		
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83		
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76		
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69		
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64		
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59		
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55		
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51		
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48		
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	126613
5°	124323
10°	117188
15°	106425
20°	93505
25°	79843
30°	66137
35°	51022
40°	36297
45°	24468
50°	13339
55°	9405
60°	8859
65°	8198
70°	7309
75°	6947
80°	5556
85°	4780

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 24468 cd/sqm

TEST NUMBER: P1252402

CATALOG NUMBER: P3AS17R409030DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.7	9.3
10°-20°	130.6	23.2
20°-30°	151.0	26.8
30°-40°	119.0	21.1
40°-50°	61.1	10.8
50°-60°	23.4	4.1
60°-70°	15.5	2.7
70°-80°	8.4	1.5
80°-90°	2.5	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	334.2	59.3
0°-40°	453.2	80.4
0°-60°	537.6	95.3
0°-90°	564.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	564.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	577	
5°	565	53
15°	469	131
25°	330	151
35°	191	119
45°	79	61
55°	25	23
65°	16	15
75°	8	8
85°	2	3
90°	0	

TEST NUMBER: P1252402

CATALOG NUMBER: P3AS17R409030DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	577.4
2.5°	574.2
5°	564.8
7.5°	548.3
10°	526.3
12.5°	500.4
15°	468.8
17.5°	436.0
20°	400.7
22.5°	364.7
25°	330.0
27.5°	295.3
30°	261.2
32.5°	226.5
35°	190.6
37.5°	157.1
40°	126.8
42.5°	101.0
45°	78.9
47.5°	57.4
50°	39.1
52.5°	28.4
55°	24.6
57.5°	22.1
60°	20.2
62.5°	17.7
65°	15.8
67.5°	13.3
70°	11.4
72.5°	9.5
75°	8.2
77.5°	6.3
80°	4.4
82.5°	3.8
85°	1.9
87.5°	1.3
90°	0.0

(END OF REPORT)