

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252450

Luminaire Tested: P3AS17R509030DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1252450
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R509030DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R50 optic, 3000K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 710.0 lumens
Efficiency: N/A
Efficacy: 33.5 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1252450

CATALOG NUMBER: P3AS17R509030DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1252450

CATALOG NUMBER: P3AS17R509030DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93
3	103	97	92	88	101	95	91	87	93	89	86		90	87	84		88
4	98	91	85	81	96	90	85	81	87	83	80		85	82	79		84
5	93	85	80	75	92	84	79	75	83	78	74		81	77	74		79
6	89	80	75	71	88	80	74	70	78	73	70		77	73	69		75
7	85	76	70	66	84	75	70	66	74	69	66		73	69	65		72
8	81	72	66	62	80	71	66	62	70	65	62		69	65	62		68
9	78	68	63	59	76	68	62	59	67	62	59		66	62	58		65
10	74	65	59	56	73	65	59	56	64	59	55		63	58	55		62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	226056
5°	221505
10°	207478
15°	185722
20°	156300
25°	119281
30°	77531
35°	45963
40°	26564
45°	13304
50°	4947
55°	3861
60°	3596
65°	3269
70°	3270
75°	3219
80°	3157
85°	3271

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13304 cd/sqm

TEST NUMBER: P1252450

CATALOG NUMBER: P3AS17R509030DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.6	13.2
10°-20°	226.3	31.9
20°-30°	222.0	31.3
30°-40°	111.8	15.7
40°-50°	35.3	5.0
50°-60°	9.1	1.3
60°-70°	6.5	0.9
70°-80°	4.0	0.6
80°-90°	1.4	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	541.8	76.3
0°-40°	653.7	92.1
0°-60°	698.1	98.3
0°-90°	710.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	710.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1031	
5°	1006	94
15°	818	226
25°	493	222
35°	172	112
45°	43	35
55°	10	9
65°	6	6
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1252450

CATALOG NUMBER: P3AS17R509030DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1030.9
2.5°	1024.6
5°	1006.3
7.5°	973.4
10°	931.8
12.5°	878.1
15°	818.1
17.5°	748.7
20°	669.8
22.5°	584.6
25°	493.0
27.5°	395.8
30°	306.2
32.5°	230.4
35°	171.7
37.5°	126.9
40°	92.8
42.5°	65.7
45°	42.9
47.5°	24.6
50°	14.5
52.5°	10.7
55°	10.1
57.5°	8.8
60°	8.2
62.5°	7.6
65°	6.3
67.5°	5.7
70°	5.1
72.5°	4.4
75°	3.8
77.5°	3.2
80°	2.5
82.5°	1.9
85°	1.3
87.5°	0.6
90°	0.0

(END OF REPORT)