

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253444

Luminaire Tested: P3AS02R259035DE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1253444
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R259035DE010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R25 optic, 3500K CCT AND, 90CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 339.0 lumens
Efficiency: N/A
Efficacy: 94.2 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.4
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1253444

CATALOG NUMBER: P3AS02R259035DE010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1253444

CATALOG NUMBER: P3AS02R259035DE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	110	113	111	110	108	107	106	105		104	103	102		100
2	112	108	106	103	110	107	104	102	104	102	100		101	99	98		98
3	109	104	101	98	107	103	100	97	100	98	96		98	96	94		96
4	106	101	97	94	104	100	96	94	98	95	92		96	93	91		94
5	103	97	93	91	101	96	93	90	95	92	90		93	91	89		92
6	100	94	90	88	99	94	90	87	92	89	87		91	88	86		90
7	98	92	88	85	97	91	87	85	90	87	84		89	86	84		88
8	95	89	85	83	94	89	85	83	88	85	82		87	84	82		86
9	93	87	83	81	92	87	83	81	86	83	80		85	82	80		84
10	91	85	81	79	90	84	81	79	84	81	78		83	80	78		83

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	371264
5°	343935
10°	266105
15°	127106
20°	41910
25°	17662
30°	6836
35°	2971
40°	973
45°	465
50°	171
55°	76
60°	44
65°	52
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 465 cd/sqm

TEST NUMBER: P1253444

CATALOG NUMBER: P3AS02R259035DE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.3	40.5
10°-20°	156.2	46.1
20°-30°	36.3	10.7
30°-40°	7.6	2.2
40°-50°	1.2	0.4
50°-60°	0.2	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	329.8	97.3
0°-40°	337.5	99.6
0°-60°	338.9	100.0
0°-90°	339.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	339.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1693	
5°	1562	137
15°	560	156
25°	73	36
35°	11	8
45°	2	1
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1253444

CATALOG NUMBER: P3AS02R259035DE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1693.1
1°	1689.7
2°	1672.1
3°	1647.4
4°	1609.7
5°	1562.5
6°	1501.9
7°	1438.4
8°	1367.3
9°	1287.0
10°	1195.1
11°	1088.5
12°	966.2
13°	832.2
14°	692.1
15°	559.9
16°	442.9
17°	345.0
18°	271.4
19°	217.1
20°	179.6
21°	150.1
22°	126.0
23°	105.2
24°	88.0
25°	73.0
27.5°	43.3
30°	27.0
32.5°	17.3
35°	11.1
37.5°	6.6
40°	3.4
42.5°	2.2
45°	1.5
47.5°	0.9
50°	0.5
52.5°	0.2
55°	0.2
57.5°	0.1
60°	0.1
62.5°	0.1
65°	0.1
67.5°	0.1
70°	0.0
72.5°	0.0



TEST NUMBER: P1253444

CATALOG NUMBER: P3AS02R259035DE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)