

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252499

Luminaire Tested: P3AS17R609030DE010 E3CB1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1252499
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-40)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R609030DE010 E3CB1MW
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 90CRI , E3CB1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1664.0 lumens
Efficiency: N/A
Efficacy: 78.5 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1252499

CATALOG NUMBER: P3AS17R609030DE010 E3CB1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1252499

CATALOG NUMBER: P3AS17R609030DE010 E3CB1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	100	98		97
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93
3	103	96	91	88	101	95	90	87	92	89	85		90	87	84		88
4	98	90	85	81	96	89	84	80	87	83	79		85	81	78		83
5	93	84	79	74	91	84	78	74	82	77	73		80	76	73		79
6	88	79	73	69	87	79	73	69	77	72	68		76	71	68		74
7	84	75	69	64	82	74	68	64	73	68	64		71	67	64		70
8	80	70	64	60	78	70	64	60	69	64	60		68	63	60		67
9	76	66	61	57	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	62	56	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	397359
5°	381597
10°	392890
15°	397936
20°	351384
25°	296122
30°	240164
35°	156413
40°	71849
45°	27538
50°	9211
55°	2447
60°	2237
65°	2024
70°	1667
75°	2203
80°	1642
85°	3271

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 27538 cd/sqm

TEST NUMBER: P1252499

CATALOG NUMBER: P3AS17R609030DE010 E3CB1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	166.9	10.0
10°-20°	480.0	28.8
20°-30°	559.9	33.6
30°-40°	361.3	21.7
40°-50°	81.0	4.9
50°-60°	8.1	0.5
60°-70°	3.8	0.2
70°-80°	2.2	0.1
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1206.8	72.5
0°-40°	1568.1	94.2
0°-60°	1657.1	99.6
0°-90°	1664.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1664.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1812	
5°	1734	167
15°	1753	480
25°	1224	560
35°	584	361
45°	89	81
55°	6	8
65°	4	4
75°	3	2
85°	1	1
90°	0	

TEST NUMBER: P1252499

CATALOG NUMBER: P3AS17R609030DE010 E3CB1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1812.1
2.5°	1782.5
5°	1733.6
7.5°	1731.0
10°	1764.5
12.5°	1786.3
15°	1752.9
17.5°	1652.5
20°	1505.8
22.5°	1352.6
25°	1223.9
27.5°	1097.8
30°	948.5
32.5°	773.5
35°	584.3
37.5°	399.0
40°	251.0
42.5°	150.6
45°	88.8
47.5°	51.5
50°	27.0
52.5°	9.0
55°	6.4
57.5°	5.1
60°	5.1
62.5°	3.9
65°	3.9
67.5°	3.9
70°	2.6
72.5°	2.6
75°	2.6
77.5°	1.3
80°	1.3
82.5°	1.3
85°	1.3
87.5°	0.0
90°	0.0

(END OF REPORT)