

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252507

Luminaire Tested: P3AS17R609030DE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1252507
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R609030DE010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 90CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1543.0 lumens
Efficiency: N/A
Efficacy: 72.8 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1252507

CATALOG NUMBER: P3AS17R609030DE010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1252507

CATALOG NUMBER: P3AS17R609030DE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93
3	103	97	92	88	101	96	91	88	93	89	86		91	87	85		88
4	98	91	85	81	96	90	85	81	88	83	80		86	82	79		84
5	93	85	80	75	92	84	79	75	83	78	74		81	77	74		79
6	89	80	74	70	87	79	74	70	78	73	70		77	72	69		75
7	85	76	70	66	83	75	69	65	74	69	65		72	68	65		71
8	81	71	65	61	79	71	65	61	70	65	61		69	64	61		68
9	77	67	62	58	76	67	61	58	66	61	57		65	61	57		64
10	73	64	58	54	72	63	58	54	63	58	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	404288
5°	381663
10°	371737
15°	363248
20°	337733
25°	301929
30°	230618
35°	133150
40°	51668
45°	21522
50°	4742
55°	726
60°	570
65°	311
70°	385
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21522 cd/sqm

TEST NUMBER: P1252507

CATALOG NUMBER: P3AS17R609030DE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	163.7	10.6
10°-20°	445.7	28.9
20°-30°	558.2	36.2
30°-40°	312.1	20.2
40°-50°	59.3	3.8
50°-60°	3.1	0.2
60°-70°	0.7	0.0
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1167.6	75.7
0°-40°	1479.7	95.9
0°-60°	1542.1	99.9
0°-90°	1543.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1543.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1844	
5°	1734	164
15°	1600	446
25°	1248	558
35°	497	312
45°	69	59
55°	2	3
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1252507

CATALOG NUMBER: P3AS17R609030DE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1843.7
1°	1836.1
2°	1812.1
3°	1783.7
4°	1757.2
5°	1733.9
6°	1716.2
7°	1701.1
8°	1689.7
9°	1679.0
10°	1669.5
11°	1660.0
12°	1649.3
13°	1636.0
14°	1620.3
15°	1600.1
16°	1575.4
17°	1547.7
18°	1516.1
19°	1480.1
20°	1447.3
21°	1412.0
22°	1375.4
23°	1336.9
24°	1294.6
25°	1247.9
26°	1192.9
27°	1131.7
28°	1062.9
29°	989.7
30°	910.8
31°	831.3
32°	749.2
32.5°	704.4
33°	664.0
34°	580.1
35°	497.4
36°	422.9
37°	344.0
37.5°	308.0
38°	272.7
39°	219.7
40°	180.5
42.5°	109.8
45°	69.4



TEST NUMBER: P1252507

CATALOG NUMBER: P3AS17R609030DE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	38.5
50°	13.9
52.5°	3.2
55°	1.9
57.5°	1.3
60°	1.3
62.5°	0.6
65°	0.6
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)