

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253456

Luminaire Tested: P3AS02R259035DE010 E3DLD1WMH

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1253456  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS02R259035DE010 E3DLD1WMH  
Description: 3in Adjustable LED luminaire with, R25 optic, 3500K CCT AND, 90CRI , E3DLD1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 201.1 lumens  
Efficiency: N/A  
Efficacy: 55.9 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1253456

CATALOG NUMBER: P3AS02R259035DE010 E3DLD1WMH

### Luminous Intensity Polar Plot



TEST NUMBER: P1253456

CATALOG NUMBER: P3AS02R259035DE010 E3DLD1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|
| RF  | 20  |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |     |    | 20 |
| RC  | 80  |     |     |     | 70  |     |     |     |     | 50  |     |     |     |     | 30  |     |     |     |    | 10 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |
| 1   | 112 | 109 | 106 | 104 | 110 | 107 | 104 | 102 | 103 | 101 | 99  | 99  | 98  | 96  | 96  | 94  | 93  | 91  |    |    |
| 2   | 106 | 100 | 96  | 92  | 104 | 99  | 94  | 91  | 95  | 92  | 89  | 92  | 89  | 87  | 89  | 87  | 85  | 83  |    |    |
| 3   | 100 | 92  | 87  | 82  | 98  | 91  | 86  | 82  | 88  | 84  | 80  | 86  | 82  | 79  | 83  | 80  | 78  | 76  |    |    |
| 4   | 94  | 85  | 79  | 74  | 92  | 84  | 78  | 74  | 82  | 77  | 73  | 80  | 76  | 72  | 78  | 74  | 71  | 70  |    |    |
| 5   | 89  | 79  | 73  | 68  | 87  | 78  | 72  | 68  | 76  | 71  | 67  | 75  | 70  | 66  | 73  | 69  | 66  | 64  |    |    |
| 6   | 84  | 74  | 67  | 62  | 82  | 73  | 67  | 62  | 71  | 66  | 62  | 70  | 65  | 61  | 69  | 64  | 61  | 59  |    |    |
| 7   | 79  | 69  | 62  | 58  | 78  | 68  | 62  | 58  | 67  | 61  | 57  | 66  | 61  | 57  | 65  | 60  | 57  | 55  |    |    |
| 8   | 75  | 65  | 58  | 54  | 74  | 64  | 58  | 53  | 63  | 57  | 53  | 62  | 57  | 53  | 61  | 56  | 53  | 51  |    |    |
| 9   | 71  | 61  | 54  | 50  | 70  | 60  | 54  | 50  | 59  | 54  | 50  | 58  | 53  | 49  | 57  | 53  | 49  | 48  |    |    |
| 10  | 68  | 57  | 51  | 47  | 67  | 57  | 51  | 47  | 56  | 50  | 47  | 55  | 50  | 46  | 54  | 50  | 46  | 45  |    |    |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 47781 |
| 5°  | 46621 |
| 10° | 43219 |
| 15° | 38479 |
| 20° | 33066 |
| 25° | 28115 |
| 30° | 23143 |
| 35° | 18042 |
| 40° | 12967 |
| 45° | 8218  |
| 50° | 4878  |
| 55° | 3364  |
| 60° | 3070  |
| 65° | 2854  |
| 70° | 2565  |
| 75° | 2372  |
| 80° | 2273  |
| 85° | 2013  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
Vertical Angle: 45°  
Luminance: 8218 cd/sqm

TEST NUMBER: P1253456

CATALOG NUMBER: P3AS02R259035DE010 E3DLD1WMH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 19.6   | 9.8       |
| 10°-20°   | 47.1   | 23.4      |
| 20°-30°   | 53.2   | 26.4      |
| 30°-40°   | 42.1   | 20.9      |
| 40°-50°   | 21.2   | 10.6      |
| 50°-60°   | 8.5    | 4.2       |
| 60°-70°   | 5.5    | 2.7       |
| 70°-80°   | 3.0    | 1.5       |
| 80°-90°   | 0.9    | 0.4       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 119.9  | 59.6      |
| 0°-40°    | 161.9  | 80.5      |
| 0°-60°    | 191.7  | 95.3      |
| 0°-90°    | 201.1  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 201.1  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 218 |      |
| 5°  | 212 | 20   |
| 15° | 170 | 47   |
| 25° | 116 | 53   |
| 35° | 67  | 42   |
| 45° | 26  | 21   |
| 55° | 9   | 9    |
| 65° | 6   | 5    |
| 75° | 3   | 3    |
| 85° | 1   | 1    |
| 90° | 0   |      |

TEST NUMBER: P1253456

CATALOG NUMBER: P3AS02R259035DE010 E3DLD1WMH

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 217.9 |
| 1°    | 217.9 |
| 2°    | 217.1 |
| 3°    | 215.8 |
| 4°    | 214.1 |
| 5°    | 211.8 |
| 6°    | 209.1 |
| 7°    | 205.8 |
| 8°    | 202.3 |
| 9°    | 198.3 |
| 10°   | 194.1 |
| 11°   | 189.3 |
| 12°   | 184.8 |
| 13°   | 179.5 |
| 14°   | 174.5 |
| 15°   | 169.5 |
| 17.5° | 155.5 |
| 20°   | 141.7 |
| 22.5° | 128.7 |
| 25°   | 116.2 |
| 27.5° | 103.9 |
| 30°   | 91.4  |
| 32.5° | 79.6  |
| 35°   | 67.4  |
| 37.5° | 56.1  |
| 40°   | 45.3  |
| 42.5° | 35.3  |
| 45°   | 26.5  |
| 47.5° | 19.8  |
| 50°   | 14.3  |
| 52.5° | 10.8  |
| 55°   | 8.8   |
| 57.5° | 8.0   |
| 60°   | 7.0   |
| 62.5° | 6.3   |
| 65°   | 5.5   |
| 67.5° | 4.8   |
| 70°   | 4.0   |
| 72.5° | 3.5   |
| 75°   | 2.8   |
| 77.5° | 2.3   |
| 80°   | 1.8   |
| 82.5° | 1.3   |
| 85°   | 0.8   |
| 87.5° | 0.3   |



TEST NUMBER: P1253456

CATALOG NUMBER: P3AS02R259035DE010 E3DLD1WMH

CANDELA DISTRIBUTION (continued):



(END OF REPORT)