

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252508

Luminaire Tested: P3AS17R609030DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1252508
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R609030DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 664.0 lumens
Efficiency: N/A
Efficacy: 31.3 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1252508

CATALOG NUMBER: P3AS17R609030DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1252508

CATALOG NUMBER: P3AS17R609030DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	84	91	86	83		88	85	82		86
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81
5	91	82	76	71	89	81	75	71	79	74	70		78	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		68
8	77	68	61	57	76	67	61	57	66	60	57		65	60	56		64
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	60	54	50	59	53	50		58	53	50		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	156786
5°	155315
10°	150788
15°	141272
20°	125031
25°	104595
30°	81987
35°	59454
40°	39560
45°	24654
50°	13339
55°	3861
60°	3596
65°	3269
70°	3206
75°	3219
80°	3157
85°	3271

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 24654 cd/sqm

TEST NUMBER: P1252508

CATALOG NUMBER: P3AS17R609030DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.4	10.0
10°-20°	172.6	26.0
20°-30°	196.8	29.6
30°-40°	139.5	21.0
40°-50°	63.3	9.5
50°-60°	13.4	2.0
60°-70°	6.5	1.0
70°-80°	4.0	0.6
80°-90°	1.4	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	435.9	65.6
0°-40°	575.4	86.7
0°-60°	652.1	98.2
0°-90°	664.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	664.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	715	
5°	706	66
15°	622	173
25°	432	197
35°	222	140
45°	80	63
55°	10	13
65°	6	6
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1252508

CATALOG NUMBER: P3AS17R609030DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	715.0
2.5°	712.5
5°	705.6
7.5°	693.6
10°	677.2
12.5°	653.8
15°	622.3
17.5°	582.5
20°	535.8
22.5°	485.3
25°	432.3
27.5°	378.0
30°	323.8
32.5°	272.0
35°	222.1
37.5°	178.0
40°	138.2
42.5°	104.8
45°	79.5
47.5°	59.3
50°	39.1
52.5°	18.3
55°	10.1
57.5°	8.8
60°	8.2
62.5°	7.6
65°	6.3
67.5°	5.7
70°	5.0
72.5°	4.4
75°	3.8
77.5°	3.2
80°	2.5
82.5°	1.9
85°	1.3
87.5°	0.6
90°	0.0

(END OF REPORT)