

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252519

Luminaire Tested: P3AS17R609030DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1252519
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-38)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R609030DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1061.0 lumens
Efficiency: N/A
Efficacy: 50.0 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1252519

CATALOG NUMBER: P3AS17R609030DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1252519

CATALOG NUMBER: P3AS17R609030DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	65	74	68	64		72	67	63		71
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	68	57	51	46	67	57	50	46	56	50	46		55	49	46		54
10	65	54	47	43	64	53	47	43	52	47	43		52	46	42		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	188340
5°	186220
10°	179778
15°	169853
20°	156557
25°	141758
30°	125867
35°	107559
40°	85532
45°	60285
50°	36024
55°	18198
60°	17499
65°	16033
70°	14874
75°	14149
80°	13007
85°	9812

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 60285 cd/sqm

TEST NUMBER: P1252519

CATALOG NUMBER: P3AS17R609030DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.5	7.5
10°-20°	209.1	19.7
20°-30°	268.5	25.3
30°-40°	248.9	23.5
40°-50°	151.6	14.3
50°-60°	50.5	4.8
60°-70°	30.7	2.9
70°-80°	17.3	1.6
80°-90°	4.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	557.1	52.5
0°-40°	806.0	76.0
0°-60°	1008.1	95.0
0°-90°	1061.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1061.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	859	
5°	846	80
15°	748	209
25°	586	268
35°	402	249
45°	194	152
55°	48	50
65°	31	31
75°	17	17
85°	4	5
90°	0	

TEST NUMBER: P1252519

CATALOG NUMBER: P3AS17R609030DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	858.9
2.5°	855.1
5°	846.0
7.5°	829.3
10°	807.4
12.5°	780.4
15°	748.2
17.5°	710.8
20°	670.9
22.5°	628.4
25°	585.9
27.5°	542.1
30°	497.1
32.5°	452.0
35°	401.8
37.5°	349.0
40°	298.8
42.5°	246.0
45°	194.4
47.5°	150.7
50°	105.6
52.5°	63.1
55°	47.6
57.5°	43.8
60°	39.9
62.5°	34.8
65°	30.9
67.5°	27.0
70°	23.2
72.5°	19.3
75°	16.7
77.5°	12.9
80°	10.3
82.5°	6.4
85°	3.9
87.5°	2.6
90°	0.0

(END OF REPORT)