

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252520

Luminaire Tested: P3AS17R609030DE010 E3DLP1GPH

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1252520  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R609030DE010 E3DLP1GPH  
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 90CRI , E3DLP1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 459.0 lumens  
Efficiency: N/A  
Efficacy: 21.7 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 21.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1252520

CATALOG NUMBER: P3AS17R609030DE010 E3DLP1GPH

### Luminous Intensity Polar Plot



TEST NUMBER: P1252520

CATALOG NUMBER: P3AS17R609030DE010 E3DLP1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 113 | 110 | 107 | 105 | 110 | 108 | 105 | 103 | 104 | 102 | 100 |  | 100 | 98  | 97  |  | 96  |
| 2   | 107 | 101 | 97  | 93  | 104 | 100 | 96  | 92  | 96  | 93  | 90  |  | 93  | 91  | 88  |  | 91  |
| 3   | 101 | 94  | 88  | 84  | 99  | 92  | 87  | 83  | 90  | 86  | 82  |  | 87  | 84  | 81  |  | 85  |
| 4   | 95  | 87  | 81  | 77  | 93  | 86  | 80  | 76  | 84  | 79  | 75  |  | 82  | 78  | 74  |  | 80  |
| 5   | 90  | 81  | 75  | 70  | 88  | 80  | 74  | 70  | 78  | 73  | 69  |  | 77  | 72  | 69  |  | 75  |
| 6   | 85  | 76  | 69  | 65  | 84  | 75  | 69  | 65  | 73  | 68  | 64  |  | 72  | 67  | 64  |  | 71  |
| 7   | 81  | 71  | 65  | 60  | 79  | 70  | 64  | 60  | 69  | 64  | 60  |  | 68  | 63  | 59  |  | 67  |
| 8   | 77  | 67  | 60  | 56  | 75  | 66  | 60  | 56  | 65  | 60  | 56  |  | 64  | 59  | 55  |  | 63  |
| 9   | 73  | 63  | 57  | 52  | 72  | 62  | 56  | 52  | 61  | 56  | 52  |  | 60  | 55  | 52  |  | 60  |
| 10  | 69  | 59  | 53  | 49  | 68  | 59  | 53  | 49  | 58  | 53  | 49  |  | 57  | 52  | 49  |  | 56  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 116328 |
| 5°  | 113713 |
| 10° | 106455 |
| 15° | 95506  |
| 20° | 82140  |
| 25° | 67915  |
| 30° | 53654  |
| 35° | 39859  |
| 40° | 27451  |
| 45° | 17211  |
| 50° | 9484   |
| 55° | 5543   |
| 60° | 5000   |
| 65° | 4255   |
| 70° | 3654   |
| 75° | 3728   |
| 80° | 3157   |
| 85° | 3271   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17211 cd/sqm

TEST NUMBER: P1252520

CATALOG NUMBER: P3AS17R609030DE010 E3DLP1GPH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 48.1   | 10.5      |
| 10°-20°   | 116.8  | 25.5      |
| 20°-30°   | 128.2  | 27.9      |
| 30°-40°   | 93.4   | 20.3      |
| 40°-50°   | 44.1   | 9.6       |
| 50°-60°   | 14.5   | 3.1       |
| 60°-70°   | 8.2    | 1.8       |
| 70°-80°   | 4.4    | 1.0       |
| 80°-90°   | 1.4    | 0.3       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 293.1  | 63.9      |
| 0°-40°    | 386.5  | 84.2      |
| 0°-60°    | 445.1  | 97.0      |
| 0°-90°    | 459.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 459.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 530 |      |
| 5°  | 517 | 48   |
| 15° | 421 | 117  |
| 25° | 281 | 128  |
| 35° | 149 | 93   |
| 45° | 56  | 44   |
| 55° | 14  | 14   |
| 65° | 8   | 8    |
| 75° | 4   | 4    |
| 85° | 1   | 1    |
| 90° | 0   |      |



TEST NUMBER: P1252520

CATALOG NUMBER: P3AS17R609030DE010 E3DLP1GPH

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 530.5 |
| 2.5°  | 527.3 |
| 5°    | 516.6 |
| 7.5°  | 500.2 |
| 10°   | 478.1 |
| 12.5° | 451.6 |
| 15°   | 420.7 |
| 17.5° | 387.3 |
| 20°   | 352.0 |
| 22.5° | 316.0 |
| 25°   | 280.7 |
| 27.5° | 245.4 |
| 30°   | 211.9 |
| 32.5° | 179.8 |
| 35°   | 148.9 |
| 37.5° | 121.1 |
| 40°   | 95.9  |
| 42.5° | 73.8  |
| 45°   | 55.5  |
| 47.5° | 40.4  |
| 50°   | 27.8  |
| 52.5° | 18.3  |
| 55°   | 14.5  |
| 57.5° | 12.6  |
| 60°   | 11.4  |
| 62.5° | 9.5   |
| 65°   | 8.2   |
| 67.5° | 6.9   |
| 70°   | 5.7   |
| 72.5° | 5.0   |
| 75°   | 4.4   |
| 77.5° | 3.2   |
| 80°   | 2.5   |
| 82.5° | 1.9   |
| 85°   | 1.3   |
| 87.5° | 0.6   |
| 90°   | 0.0   |

(END OF REPORT)