

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252525

Luminaire Tested: P3AS17R609030DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1252525
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R609030DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 936.0 lumens
Efficiency: N/A
Efficacy: 44.2 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1252525

CATALOG NUMBER: P3AS17R609030DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1252525

CATALOG NUMBER: P3AS17R609030DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	107	101	97	93	104	100	96	92	96	93	90		93	91	88		91
3	101	94	88	84	99	92	87	83	90	86	82		87	84	81		85
4	95	87	81	77	93	86	80	76	84	79	75		82	78	74		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	76	69	65	84	75	69	65	73	68	64		72	67	64		71
7	81	71	65	60	79	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	60	56		64	59	55		63
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		60
10	69	59	53	49	68	59	53	49	58	53	49		57	52	49		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	237218
5°	231895
10°	217097
15°	194780
20°	167501
25°	138492
30°	109435
35°	81271
40°	55962
45°	35104
50°	19309
55°	11316
60°	10175
65°	8665
70°	7437
75°	7625
80°	6440
85°	6542

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 35104 cd/sqm

TEST NUMBER: P1252525

CATALOG NUMBER: P3AS17R609030DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.1	10.5
10°-20°	238.3	25.5
20°-30°	261.4	27.9
30°-40°	190.4	20.3
40°-50°	89.9	9.6
50°-60°	29.5	3.1
60°-70°	16.7	1.8
70°-80°	9.0	1.0
80°-90°	2.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	597.7	63.9
0°-40°	788.1	84.2
0°-60°	907.5	97.0
0°-90°	936.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	936.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1082	
5°	1054	98
15°	858	238
25°	572	261
35°	304	190
45°	113	90
55°	30	29
65°	17	17
75°	9	9
85°	3	3
90°	0	

TEST NUMBER: P1252525

CATALOG NUMBER: P3AS17R609030DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1081.8
2.5°	1075.3
5°	1053.5
7.5°	1020.0
10°	975.0
12.5°	921.0
15°	858.0
17.5°	789.8
20°	717.8
22.5°	644.4
25°	572.4
27.5°	500.4
30°	432.2
32.5°	366.6
35°	303.6
37.5°	247.0
40°	195.5
42.5°	150.5
45°	113.2
47.5°	82.3
50°	56.6
52.5°	37.3
55°	29.6
57.5°	25.7
60°	23.2
62.5°	19.3
65°	16.7
67.5°	14.1
70°	11.6
72.5°	10.3
75°	9.0
77.5°	6.4
80°	5.1
82.5°	3.9
85°	2.6
87.5°	1.3
90°	0.0

(END OF REPORT)