

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253511

Luminaire Tested: P3AS02R359035DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1253511
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R359035DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R35 optic, 3500K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 99.0 lumens
Efficiency: N/A
Efficacy: 27.5 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1253511
CATALOG NUMBER: P3AS02R359035DE010 E3DLD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1253511
 CATALOG NUMBER: P3AS02R359035DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59			
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51			
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	22608
5°	22144
10°	20730
15°	18615
20°	16195
25°	13791
30°	11546
35°	9209
40°	6641
45°	4217
50°	2286
55°	1606
60°	1491
65°	1401
70°	1346
75°	1101
80°	1137
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4217 cd/sqm



TEST NUMBER: P1253511
 CATALOG NUMBER: P3AS02R359035DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	9.4	9.5
10°-20°	22.8	23.0
20°-30°	26.1	26.4
30°-40°	21.3	21.5
40°-50°	10.8	10.9
50°-60°	4.0	4.0
60°-70°	2.7	2.7
70°-80°	1.5	1.5
80°-90°	0.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	58.3	58.9
0°-40°	79.6	80.4
0°-60°	94.4	95.3
0°-90°	99.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	99.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	103	
5°	101	9
15°	82	23
25°	57	26
35°	34	21
45°	14	11
55°	4	4
65°	3	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1253511
CATALOG NUMBER: P3AS02R359035DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	103.1
1°	103.0
2°	102.8
3°	102.3
4°	101.5
5°	100.6
6°	99.3
7°	98.1
8°	96.5
9°	94.9
10°	93.1
11°	91.1
12°	89.1
13°	86.7
14°	84.3
15°	82.0
17.5°	75.7
20°	69.4
22.5°	62.9
25°	57.0
27.5°	51.3
30°	45.6
32.5°	40.0
35°	34.4
37.5°	28.7
40°	23.2
42.5°	18.1
45°	13.6
47.5°	9.8
50°	6.7
52.5°	4.9
55°	4.2
57.5°	3.8
60°	3.4
62.5°	3.1
65°	2.7
67.5°	2.3
70°	2.1
72.5°	1.7
75°	1.3
77.5°	1.1
80°	0.9
82.5°	0.6
85°	0.4
87.5°	0.2



TEST NUMBER: P1253511
CATALOG NUMBER: P3AS02R359035DE010 E3DLD1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)