

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253545

Luminaire Tested: P3AS02R409035DE010 E3DLD1LI

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1253545  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS02R409035DE010 E3DLD1LI  
Description: 3in Adjustable LED luminaire with, R40 optic, 3500K CCT AND, 90CRI , E3DLD1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 224.1 lumens  
Efficiency: N/A  
Efficacy: 62.2 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1253545  
CATALOG NUMBER: P3AS02R409035DE010 E3DLD1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P1253545  
 CATALOG NUMBER: P3AS02R409035DE010 E3DLD1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			91
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			69
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			64
6	84	74	67	62	82	73	66	62	71	66	61	70	65	61	68	64	61	59			59
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			55
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51			51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			48
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	44			44

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	50281
5°	49373
10°	46537
15°	42270
20°	37127
25°	31720
30°	26283
35°	20264
40°	14427
45°	9706
50°	5288
55°	3747
60°	3508
65°	3269
70°	2885
75°	2796
80°	2273
85°	2013

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 9706 cd/sqm



TEST NUMBER: P1253545  
 CATALOG NUMBER: P3AS02R409035DE010 E3DLD1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	20.9	9.3
10°-20°	51.9	23.1
20°-30°	60.0	26.8
30°-40°	47.3	21.1
40°-50°	24.2	10.8
50°-60°	9.3	4.1
60°-70°	6.1	2.7
70°-80°	3.4	1.5
80°-90°	1.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	132.8	59.2
0°-40°	180.0	80.3
0°-60°	213.6	95.3
0°-90°	224.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	224.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	229	
5°	224	21
15°	186	52
25°	131	60
35°	76	47
45°	31	24
55°	10	9
65°	6	6
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1253545  
CATALOG NUMBER: P3AS02R409035DE010 E3DLD1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	229.3
2.5°	228.1
5°	224.3
7.5°	217.8
10°	209.0
12.5°	198.7
15°	186.2
17.5°	173.2
20°	159.1
22.5°	144.9
25°	131.1
27.5°	117.3
30°	103.8
32.5°	90.0
35°	75.7
37.5°	62.4
40°	50.4
42.5°	40.1
45°	31.3
47.5°	22.8
50°	15.5
52.5°	11.3
55°	9.8
57.5°	8.8
60°	8.0
62.5°	7.0
65°	6.3
67.5°	5.3
70°	4.5
72.5°	3.8
75°	3.3
77.5°	2.5
80°	1.8
82.5°	1.5
85°	0.8
87.5°	0.5
90°	0.0

(END OF REPORT)