

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253548

Luminaire Tested: P3AS02R409035DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1253548
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R409035DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R40 optic, 3500K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 224.1 lumens
Efficiency: N/A
Efficacy: 62.2 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1253548

CATALOG NUMBER: P3AS02R409035DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1253548

CATALOG NUMBER: P3AS02R409035DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	98	96		96
2	106	100	96	92	104	98	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	81	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	75	72		78
5	89	79	73	68	87	78	72	67	76	71	67		75	70	66		73
6	84	74	67	62	82	73	66	62	71	66	61		70	65	61		68
7	79	69	62	57	78	68	62	57	67	61	57		65	60	57		64
8	75	64	58	53	74	64	57	53	63	57	53		62	56	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	51	46	66	56	50	46	56	50	46		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	50281
5°	49373
10°	46537
15°	42270
20°	37127
25°	31720
30°	26283
35°	20264
40°	14427
45°	9706
50°	5288
55°	3747
60°	3508
65°	3269
70°	2885
75°	2796
80°	2273
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9706 cd/sqm

TEST NUMBER: P1253548

CATALOG NUMBER: P3AS02R409035DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	20.9	9.3
10°-20°	51.9	23.1
20°-30°	60.0	26.8
30°-40°	47.3	21.1
40°-50°	24.2	10.8
50°-60°	9.3	4.1
60°-70°	6.1	2.7
70°-80°	3.4	1.5
80°-90°	1.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	132.8	59.2
0°-40°	180.0	80.3
0°-60°	213.6	95.3
0°-90°	224.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	224.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	229	
5°	224	21
15°	186	52
25°	131	60
35°	76	47
45°	31	24
55°	10	9
65°	6	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1253548

CATALOG NUMBER: P3AS02R409035DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	229.3
2.5°	228.1
5°	224.3
7.5°	217.8
10°	209.0
12.5°	198.7
15°	186.2
17.5°	173.2
20°	159.1
22.5°	144.9
25°	131.1
27.5°	117.3
30°	103.8
32.5°	90.0
35°	75.7
37.5°	62.4
40°	50.4
42.5°	40.1
45°	31.3
47.5°	22.8
50°	15.5
52.5°	11.3
55°	9.8
57.5°	8.8
60°	8.0
62.5°	7.0
65°	6.3
67.5°	5.3
70°	4.5
72.5°	3.8
75°	3.3
77.5°	2.5
80°	1.8
82.5°	1.5
85°	0.8
87.5°	0.5
90°	0.0

(END OF REPORT)