

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253573

Luminaire Tested: P3AS02R459035DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1253573
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R459035DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R45 optic, 3500K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 217.1 lumens
Efficiency: N/A
Efficacy: 60.3 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1253573

CATALOG NUMBER: P3AS02R459035DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1253573

CATALOG NUMBER: P3AS02R459035DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	92	86	82	97	90	85	81	88	83	80		85	81	78		83
4	94	85	78	74	92	84	78	73	81	76	72		79	75	71		77
5	88	79	72	67	86	78	71	67	76	70	66		74	69	65		72
6	83	73	66	61	81	72	66	61	71	65	61		69	64	60		68
7	78	68	61	57	77	67	61	56	66	60	56		65	60	56		64
8	74	64	57	52	73	63	57	52	62	56	52		61	56	52		60
9	70	60	53	49	69	59	53	49	58	52	48		57	52	48		56
10	67	56	50	45	66	56	49	45	55	49	45		54	49	45		53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	46005
5°	45190
10°	42774
15°	39001
20°	34490
25°	29953
30°	25700
35°	21415
40°	15973
45°	9768
50°	4537
55°	3555
60°	3421
65°	3113
70°	2885
75°	2796
80°	2526
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9768 cd/sqm

TEST NUMBER: P1253573

CATALOG NUMBER: P3AS02R459035DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	19.2	8.8
10°-20°	47.8	22.0
20°-30°	56.8	26.2
30°-40°	49.4	22.7
40°-50°	24.8	11.4
50°-60°	8.6	4.0
60°-70°	6.0	2.8
70°-80°	3.4	1.6
80°-90°	1.0	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	123.8	57.0
0°-40°	173.2	79.8
0°-60°	206.6	95.2
0°-90°	217.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	217.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	210	
5°	205	19
15°	172	48
25°	124	57
35°	80	49
45°	32	25
55°	9	9
65°	6	6
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1253573

CATALOG NUMBER: P3AS02R459035DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	209.8
2.5°	208.8
5°	205.3
7.5°	199.8
10°	192.1
12.5°	182.6
15°	171.8
17.5°	159.8
20°	147.8
22.5°	135.5
25°	123.8
27.5°	112.5
30°	101.5
32.5°	91.0
35°	80.0
37.5°	68.3
40°	55.8
42.5°	43.5
45°	31.5
47.5°	20.8
50°	13.3
52.5°	10.3
55°	9.3
57.5°	8.5
60°	7.8
62.5°	7.0
65°	6.0
67.5°	5.3
70°	4.5
72.5°	3.8
75°	3.3
77.5°	2.5
80°	2.0
82.5°	1.5
85°	0.8
87.5°	0.5
90°	0.0

(END OF REPORT)