

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253625

Luminaire Tested: P3AS02R559035DE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1253625
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R559035DE010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R55 optic, 3500K CCT AND, 90CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 273.1 lumens
Efficiency: N/A
Efficacy: 75.9 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1253625

CATALOG NUMBER: P3AS02R559035DE010 E3DL1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1253625

CATALOG NUMBER: P3AS02R559035DE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	111	108	106		111	108	106	104		104	103	101		101	99	98		97	96	95
2	108	103	99	95		106	101	97	94		98	95	92		95	92	90		92	90	88
3	102	96	91	87		100	94	90	86		92	88	85		89	86	83		87	84	82
4	97	90	84	80		95	88	83	79		86	82	78		84	81	78		82	79	77
5	92	84	78	74		91	83	78	74		81	77	73		80	75	72		78	74	72
6	88	79	73	69		86	78	73	68		77	72	68		75	71	68		74	70	67
7	84	74	68	64		82	74	68	64		72	67	64		71	67	63		70	66	63
8	80	70	64	60		78	70	64	60		69	63	60		67	63	60		67	62	59
9	76	66	61	57		75	66	60	56		65	60	56		64	59	56		63	59	56
10	72	63	57	53		71	62	57	53		62	57	53		61	56	53		60	56	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	74972
5°	74202
10°	71653
15°	66243
20°	57148
25°	45148
30°	32030
35°	20639
40°	12395
45°	6977
50°	3753
55°	1338
60°	1228
65°	1193
70°	1154
75°	1101
80°	1010
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6977 cd/sqm

TEST NUMBER: P1253625

CATALOG NUMBER: P3AS02R559035DE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	31.7	11.6
10°-20°	80.7	29.5
20°-30°	84.6	31.0
30°-40°	49.3	18.1
40°-50°	18.5	6.8
50°-60°	4.4	1.6
60°-70°	2.3	0.8
70°-80°	1.3	0.5
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	196.9	72.1
0°-40°	246.3	90.2
0°-60°	269.1	98.5
0°-90°	273.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	273.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	342	
5°	337	32
15°	292	81
25°	187	85
35°	77	49
45°	22	18
55°	4	4
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1253625

CATALOG NUMBER: P3AS02R559035DE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	341.9
2.5°	340.9
5°	337.1
7.5°	331.1
10°	321.8
12.5°	308.8
15°	291.8
17.5°	270.2
20°	244.9
22.5°	216.6
25°	186.6
27.5°	155.8
30°	126.5
32.5°	99.9
35°	77.1
37.5°	58.6
40°	43.3
42.5°	31.1
45°	22.5
47.5°	16.3
50°	11.0
52.5°	6.3
55°	3.5
57.5°	3.0
60°	2.8
62.5°	2.5
65°	2.3
67.5°	2.0
70°	1.8
72.5°	1.5
75°	1.3
77.5°	1.0
80°	0.8
82.5°	0.5
85°	0.3
87.5°	0.3
90°	0.0

(END OF REPORT)